

## Analytical scales ALS



### Application:


Compact dimensions, advantageous in limited space

### Execution:

- Fast and efficient working thanks to the graphic display. Simple plain text user guidance in the display in languages DE, GB, FR, IT, ES, PT
- CAL calibration program for setting accuracy
- Short settling time: Stable weighing values within approx. 4 s
- Weighing with tolerance range (checkweighing): Input of an upper/lower limit. An optical and acoustic signal supports portioning, dosing and sorting
- Dosing aid: High-efficiency mode and other filter settings can be selected
- Internal memory for complete recipes with name and setpoint of the recipe components. Display-supported user guidance
- Ergonomically optimised control panel for left- and right-handed users
- Large glass wind guard with 3 sliding doors for convenient access to the weighing goods
- Compact dimensions, advantageous in limited space
- with a large weighing range, graphic display and convenient recipe function

### Delivery:

with storm cuff, power supply unit and work protection hood



<b>Art. no.</b>	<b>49000 066</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	ALS 160-4A
<b>Type description</b>	ALS 160-4A
<b>Max. weight measuring range</b>	160 g
<b>Digit increment, weight</b>	0.0001 g
<b>Digit height</b>	17 mm
<b>Plate diameter</b>	80 mm
<b>Material of cover panel</b>	Stainless steel
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	10 mg
<b>Reproducibility</b>	0.0001 g
<b>Linearity</b>	0.0003 g
<b>Data transmission type</b>	RS232
<b>Housing dimensions (LxWxH)</b>	210 x 340 x 330 mm
<b>Display type</b>	Graphic LCD
<b>Gross Weight</b>	9.000 kg
<b>Product Group</b>	447

### EAN

4045761098763