

Heavy Duty Fuse Clip, 6.3x32 mm, 600 VAC/VDC, 32 A





Solder THT version tin-plated

Solder THT version silver-plated

600 VAC/DC · 32 A (UL)

See below:

Approvals and Compliances

Description

- Solder mounting

Unique Selling Proposition

- Unique 600 VAC/VDC and 32 A
- Minimal power loss due to strong clamping force

Applications

- Photovoltaic
- Applications for high currents and voltages
- Equipment with three-phase supply (400 VAC)

References

Fuseholder to A12FA 660V; FSF 6.3x32; FST 6.3x32; SA 6.3x32; SHF 6.3x32; SHT 6.3x32; SP 6.3x32; SPT 6.3x32; SUT 6.3x32

Weblinks

pdf datasheet, html-datasheet, General Product Information, Packaging details, Distributor-Stock-Check, Detailed request for product, Microsite

Technical Data

Fuse-Link	6.3 x 32 mm
Mounting	PCB
Terminal	Solder THT
Rated Voltage	600 VAC/DC
Rated current	32 A (UL)
Admissible Ambient Air Temp.	-55 °C to 155 °C 1)
Material: Terminals	Copper alloy, silver-plated / tin-plated 1)
Storage Conditions	0°C to 60°C, max. 70% r.h.
	·

Soldering Methods	Wave
-	Soldering Profile
Solderability	245°C / 3 sec acc. to IEC 60068-2-20,
·	Test Ta, method 1
Resistance to Soldering Heat	260°C / 10 sec acc. to IEC 60068-2-20,
	Test Tb, method 1A
Contact Resistance	≤ 10 mΩ at 20 mV

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: CQP

Approval Logo	Certificates	Certification Body	Description
c FL °us	UL Approvals	UL	UL File Number: E39328

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
(h)	Designed according to	UL 4248-1	Fuseholder general requirements
GF Group	Designed according to	CSA C22.2 no. 4248.1	Fuseholder general requirements

¹⁾ Details see table of variants

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technologyequipment.


Compliances


The product complies with following Guide Lines

The Property of the Property o			
Details	Initiator	Description	
CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.	
RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU	
China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.	
REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.	
	CE declaration of conformity RoHS China RoHS	CE declaration of conformity SCHURTER AG ROHS SCHURTER AG China ROHS SCHURTER AG	

Dimension [mm]

8.2 mm





Drilling diagram

product selected for their own applications.

All Variants

• Tin-plated 8040.0001 • Silver-plated 8040.0003	Clip	Material: Anschlüsse	Order Number
 Silver-plated 8040 0003 	•	Tin-plated	8040.0001
Oliver plated 0040.0000	•	Silver-plated	8040.0003

Most Popular.

Availability for all products can be searched realtime:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging Unit Bulk (1000 pcs.)