

| Photo | Part number | Description | Target application | MI 3155 | MI 3152 | MI 3152H | MI 3102 BT | MI 3102H BT | MI 3100 SE | MI 3125 BT | MI 3108 | MI 3109 | MI 3121 | MI 3122 | MI 3123 | MI 3110 | MI 2088 | MI 2093 | A 1143 | | |
|---|-------------|---|--|---------|---------|----------|------------|-------------|------------|------------|---------|---------|---------|---------|---------|---------|---------|---------|--------|---|---|
|  | A 1021 | Test lead, 4 x 1 m | 4-wire test lead for measurements on electrical installations. | | | | | | | | | | | | | | | | | • | |
|  | A 1011 | Test lead, 3 x 1.5 m | 3-wire test lead for measurements on single or three phase electrical installations. | • | • | • | • | • | • | • | • | | | • | | • | | | | | |
|  | A 1055 | Test lead, 2 x 1.5 m | 2-wire test lead for continuity and insulation resistance measurements on electrical installations. | • | | • | | • | | | | | | • | | | | | | | |
|  | A 1385 | PV fused test lead | Test cable for simultaneous AC/DC power and efficiency measurements of PV inverters. | | | | | | | | | • | • | | | | | | | | |
|  | S 2001 | Earth test set, 4-wire, 20 m | Earth test set for earth resistance measurement on distance up to 20 m; set includes: test lead, 4 x 1 m; test lead, 20 m, 2 pcs; test lead, 4 m, 2 pcs; earth spikes, 4 pcs; soft carrying bag. | | | | | | | | | | | | | | | | | | • |
|  | S 2002 | Earth test set, 4-wire, 50 m | Earth test set for earth resistance measurement on distance up to 50 m; set includes: test lead, 4 x 1 m; test lead, 50 m, 2 pcs; test lead, 4 m, 2 pcs; test lead, 1 m, 2 pcs; earth spikes, 4 pcs; carrying bag. | | | | | | | | | | | | | | | | | | • |
|  | S 2041 | Earth test set, 4-wire, 50 m (for Smartec) | Earth test set for earth resistance measurement on distance up to 50 m; set includes: test lead, 50 m, 2 pcs; test lead, 4 m, 2 pcs; test lead, 1 m, 2 pcs; earth spikes, 4 pcs; soft carrying bag. | | | | | | | | | | | | | | | | | | • |
|  | S 2026 | Earth test set, 3-wire, 20 m | Earth test set for earth resistance measurement on distance up to 20 m; set includes: test lead, 20 m, 2 pcs; test lead, 4,5 m; earth spikes, 2 pcs; soft carrying bag. | | | | • | • | • | • | • | | | | | | | | | | |
|  | S 2027 | Earth test set, 3-wire, 50 m | Earth test set for earth resistance measurement on distance up to 50 m; set includes: test lead, 50 m, 2 pcs; test lead, 4,5 m; test lead, 1 m, 2 pcs; earth spikes, 2 pcs; soft carrying bag. | • | • | • | • | • | • | • | • | | | | | | | | | | |
|  | S 2058 | Insulation test plates | Two in one: Test plates for measurement of floor and wall insulation, $\Delta 625 \text{ cm}^2$ (acc. to EN 60364-6) and measurement of semi conductivity, 2,5 kg, $\varnothing 65 \text{ mm}$ (acc. to EN 61340-5-1). | | • | | • | • | • | • | | | • | | | • | • | | | | |
|  | A 1290 | PC SW EuroLink PRO Plus with USB and RS232-PS/2 cable | Professional PC Software EuroLink PRO Plus enables downloading, data management and complete test report preparation. Delivered with RS232-PS/2 and USB communication cables. | | | | | | | | | | • | • | • | | | | | | |

• Option