

## Data sheet for SIMOTICS S-1FL6

MLFB-Ordering data

1FL6034-2AF21-1AA1



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Engineering data

Rated speed	3000 rpm
Rated torque (100 K)	1.27 Nm
Rated current	2.6 A
Rated power	0.40 kW / 0.54 hp
Max. speed	5000 rpm
Maximum torque	3.82 Nm
Max. current	7.8 A
Static torque	1.27 Nm
Moment of inertia	0.351 kgcm <sup>2</sup>

### Physical constants

Torque constant	0.49 Nm/A
Thermal class	B (130 °C)
Net weight	1.46 kg

### Ambient conditions

#### Ambient temperature

Operation	0 ... 40 °C
-----------	-------------

#### Relative humidity

Max. operation	90 % RH maximum (no condensation at 30 °C)
----------------	--

### Standards

Compliance with standards	CE, EAC
---------------------------	---------

### Mechanical data

Motor type	Low Inertia
Motor type	Permanent-magnet synchronous motor
Shaft height	30
Encoder system	Incremental encoder TTL, 2500 S/R (13 bit)
Cooling	Natural cooling
Shaft extension	Feather key
Radial runout tolerance	Class N
Vibration severity grade	Grade A
Degree of protection	IP65
Design acc. to Code I	IM B5 (IM V1, IM V3)
Connection type	Cable outlet