## **Fiber-Optic Cable Sensor**


# ODX202P0008

Part Number



- Key potentiometer, teach-in
- Large detection and working range
- Recognition of transparent objects
- Reflex and through-beam operation mode are possible

wenglor fiber-optic cables are connected to these sensors. The easy to use teach-in function allows for fine sensor adjustment, so that even transparent objects can be reliably recognized in through-beam mode operation. The scanning width is automatically adapted to each individual application via external teach-in. The sensors can be easily mounted to standard DIN rails.




#### **Technical Data**

Optical Data			
Switching Hysteresis	< 15 %		
Light Source	Red Light		
Wavelength	660 nm		
Service Life (T = +25 °C)	100000 h		
Max. Ambient Light	10000 Lux		
Electrical Data			
Supply Voltage	1030 V DC		
Current Consumption (Ub = 24 V)	< 40 mA		
Switching Frequency	2 kHz		
Response Time	250 μs		
On-/Off-Delay	0200 ms		
Temperature Drift	< 10 %		
Temperature Range	-2560 °C		
Switching Output Voltage Drop	< 2,5 V		
Switching Output/Switching Current	200 mA		
Short Circuit Protection	yes		
Reverse Polarity Protection	yes		
Overload Protection	yes		
Teach Mode	NT, MT, ZT, DT, TP		
Protection Class	III		
Mechanical Data			
Setting Method	Teach-In		
Housing Material	Plastic		
Full Encapsulation	yes		
Degree of Protection	IP65		
Connection	M8 × 1; 3-pin		
DIN-Rail mounting	35 mm		
Safety-relevant Data			
MTTFd (EN ISO 13849-1)	1499,88 a		
Configurable as PNP/NPN/Push-Pull	•		
Switchable to NC/NO	Ŏ		
Connection Diagram No.	772		
Control Panel No.	X1		
Suitable Connection Equipment No.	8		
Suitable Fiber-Optic Cable Adapter No.	03		


### **Complementary Products**

Glass Fiber-Optic Cable
Plastic Fiber-Optic Cable






#### Ctrl. Panel



- 01 = Switching Status Indicator
- 02 = Contamination Warning
- 07 = Selector Switch
- 24 = Plus Button
- 25 = Minus Button



_eger	ia	F	PT	Platinum measuring resistor	ENARS	∞ Encoder A/Ā (TTL)
+	Supply Voltage +	r	nc	not connected	ENBRS	Encoder B/B (TTL)
-	Supply Voltage 0 V	l	J	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)	(	J	Test Input inverted	ENB	Encoder B
A	Switching Output	(NO)	N	Trigger Input	Amin	Digital output MIN
Ā		(NC)	W —	Ground for the Trigger Input	Амах	Digital output MAX
V	Contamination/Error Output	(NO)	2	Analog Output	Аок	Digital output OK
V	Contamination/Error Output	(NC)	o –	Ground for the Analog Output	SY In	Synchronization In
E	Input (analog or digital)	E	3Z	Block Discharge	SY OL	T Synchronization OUT
Т	Teach Input	,	Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)		a	Valve Control Output +	М	Maintenance
S	Shielding	k	)	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path		SY.	Synchronization	Wire	Colors according to DIN IEC 757
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black
RDY	Ready	E	Ξ+	Receiver-Line	BN	Brown
GND	Ground	8	3+	Emitter-Line	RD	Red
CL	Clock	-	÷	Grounding	OG	Orange
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow
•	IO-Link	F	Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet	•	Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input	E	Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output	L	_a	Emitted Light disengageable	GY	Grey
Signal	Signal Output	-	Mag	Magnet activation	WH	White
BI_D+/-	Ethernet Gigabit bidirect, data			Input confirmation	PK	Pink
ENors42	Encoder 0-pulse 0-0 (TTL)		EDM .	Contactor Monitoring	GNY	Green/Yellow









