


# SM9604

## Magnetic-inductive flow meter

SMN32XGX50KG/US-100



### Product characteristics

Number of inputs and outputs	Number of analogue outputs: 2			
Measuring range	5...300 l/min	0.3...18 m³/h	80...4755 gph	1.3...79.3 gpm
Process connection	threaded connection 1 1/2 NPT DN40			

# SM9604

## Magnetic-inductive flow meter

SMN32XGX50KG/US-100



Application									
Special feature	Gold-plated contacts								
Application	empty pipe detection; for industrial applications								
Media	conductive liquids; water; hydrous media								
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)								
Medium temperature	-10...70 °C		14...158 °F						
Pressure rating	[bar]	16							
Pressure rating	[psi]	232							
MAWP (for applications according to CRN)	[bar]	16.5							
Electrical data									
Operating voltage	[V]	18...32 DC; (according to EN 50178 SELV/PELV)							
Current consumption	[mA]	< 150							
Protection class	III								
Reverse polarity protection	yes								
Power-on delay time	[s]	5							
Inputs / outputs									
Number of inputs and outputs	Number of analogue outputs: 2								
Outputs									
Total number of outputs	2								
Output signal	analogue signal								
Number of analogue outputs	2								
Analogue current output	[mA]	4...20; ( $\leq 22 \text{ mA}$ )							
Max. load	[Ω]	500							
Measuring/setting range									
Measuring range	5...300 l/min	0.3...18 m³/h	80...4755 gph	1.3...79.3 gpm					
Display range	-360...360 l/min	-21.6...21.6 m³/h	-5705...5705 gph	-95.1...95.1 gpm					
Resolution	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm					
Analogue start point ASP	0...240 l/min	0...14.4 m³/h	0...3800 gph	0...63.4 gpm					
Analogue end point AEP	60...300 l/min	3.6...18 m³/h	955...4755 gph	15.9...79.3 gpm					
Low flow cut-off LFC	< 15 l/min	< 0.9 m³/h	< 240 gph	< 4 gpm					
In steps of	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm					
Measuring dynamics	1:60								
Temperature monitoring									
Measuring range	-20...80 °C		-4...176 °F						
Display range	-40...100 °C		-40...212 °F						
Resolution	0.2 °C		0.5 °F						
Analogue start point	-20...60 °C		-4...140 °F						
Analogue end point	0...80 °C		32...176 °F						
In steps of	0.2 °C		0.5 °F						

# SM9604



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW
Temperature monitoring		
Temperature drift		± 0,0333 °C / K; ± 0,0599 °F / K
Accuracy [K]		± 1 (25 °C; Q > 15 l/min) / ± 1 (77 °F; Q > 4 gpm)
Response times		
Flow monitoring		
Response time [s]		0.35; (dAP = 0)
Damping for the switching output dAP [s]		0...5
Temperature monitoring		
Dynamic response T05 / T09 [s]		T09 = 3 (Q > 15 l/min) / T09 = 3 (Q > 4 gpm)
Software / programming		
Parameter setting options		
display can be deactivated; Display unit; empty pipe detection		
Operating conditions		
Ambient temperature		-10...60 °C
Storage temperature		-25...80 °C
Protection		IP 65; IP 67
Tests / approvals		
EMC		DIN EN 60947-5-9 DIN EN 61000-6-2
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF [years]		78
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight [g]		2745
Materials		stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEI; FKM; PBT-GF20; TPE-U
Materials (wetted parts)		stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEEK; FKM
Process connection		threaded connection 1 1/2 NPT DN40
Displays / operating elements		
Display	Display unit	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F)
	function display	1 x LED, yellow (10³)
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit
Display unit		l/min; m³/h; gpm; gph; °C; °F
Accessories		
Accessories (supplied)		Label

# SM9604



## Magnetic-inductive flow meter

SMN32XGX50KG/US-100

### Remarks

Remarks

MW = measured value

Pack quantity

MEW = Final value of the measuring range


1 pcs.

### Electrical connection

Connector: 1 x M12; Contacts: gold-plated



### Connection



colours to DIN EN 60947-5-2

OUT1: analogue output Temperature monitoring

OUT2: analogue output volumetric flow quantity monitoring

Core colours :

BK = black

BN = brown

BU = blue

WH = white


## Magnetic-inductive flow meter

SMN32XGX50KG/US-100


### Diagrams and graphs

Pressure loss

dP [mbar] DN50



dP [psi]



dP Pressure loss

Q volumetric flow quantity