



Construction and working characteristics

- 3 ways poppet valve.
- Body made with light alloy.
- Wall mounting possibility with M6 screws protected by covers.
- Double action handle for valve opening: pushing and rotating (clockwise).
- Simple rotate the valve handle counter clockwise for valve closing and down stream circuit discharging.
- Possibility to lock the valve in the discharging position by fitting in a padlock in the proper seat.

Technical characteristics

Connections	G 1/2"
Max. inlet pressure	13 bar - 1,3 MPa
Max. ambient temperature	50°C
Weight	gr. 550
Assembly position	Any
Nominal flow at 6 bar with $D_p=1$	2500 NI/min
Wall mounting screws	M6
Handle opening and closing angle	90°
Max. fitting torque	40 Nm

Important note: the preventive or programmed maintenance of this product is not foreseen considering the elaborated assembling and the specific "PNEUMAX" testing; therefore, call the producer or its representative in case of necessity.

Ordering code

17330 .

A = Not lockable handle
B = Lockable handle

Example: **17330.B**
Shut-off valve size 3 complete with lockable handle.