

## Data Sheet

Weller part no. T0053368870

Description: High power station for all through hole and surface mount rework, type WR3000M ER

Comprises: WR3M power unit  
DSX 120 desoldering iron 120 W rated  
WDH 30 safety rest  
WP 120 soldering iron 120 W rated  
WDH 10 safety rest  
HAP 200 hot air pencil 200 W rated  
WDH 30 Safety rest

Supply voltage 230V 50Hz

Tool operating voltages 24V 50Hz (all tools)

Mains lead UK + Euro

Power rating 360W

Protection Class 1

Temperature range WP 120 soldering iron 50 C – 450 C heat up time to 350C – ca 14 sec  
DSX 120 desoldering iron 100 C – 450 C heat up time to 350C – ca 35sec  
HAP 200 hot air pencil 50 C – 550 C

Hot air delivery variable 0 – 15 l/min

Temperature accuracy Solder / Desolder tools, +/- 9C  
Hot air pencil, +/- 30C

Temperature display Digital red LCD

Temperature set up /down push buttons

USB interface for firmware downloads

ESD safe

Compliance IPC- J001

Consumables: soldering iron tips XT series

Desoldering nozzles XDS series

Hot air nozzles flat, round, DIL, and Quad