

### RoHS Compliant



#### **Description**

The resistors are constructed in a high grade ceramic body (aluminium oxide). Internal metal electrodes are added at each end and connected by a resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to within tolerance by laser cutting of this resistive layer


#### Features:

- High reliability and stability ±1%
- Sulfuration resistant 1,000 ppm
- · Automotive grade AEC Q-200 compliant
- 100% CCD inspection
- Lead-free

#### **Applications:**

Automotive application
Consumer electrical equipment
EDP, computer application
Telecom application

The resistive layer is covered with a protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a Tin (lead free) alloy



Construction of a Chip-R

#### **Quick Reference Data**

Item	General Specification	
Series no.	MCSR04	
Size code	04	02
Resistance range	1Ω to 10MΩ (±5% tolerance), Jumper 1Ω to 10MΩ (±1% tolerance)	
Resistance tolerance	±1% E96 / E24	±5% E24
TCR (ppm/°C) R > 1MΩ $10\Omega < R \le 1M\Omega$ R $\le 10\Omega$	≤ +200 ≤ +100 -200 to +400	
Maximum dissipation at Tamb = 70°C	1/16W	
Maximum operation voltage (DC or RMS)	50V	
Maximum overload voltage (DC or RMS)	100V	
Climatic category (IEC 60068)	55/155/56	






#### Note:

- 1. This is the maximum voltage that may be continuously supplied to the resistor element, see "IEC publication 60115-8"
- 2. Maximum operation voltage: So called RCWV (rated continuous working voltage) is determined by

RCWV = √Rated Power × Resistance Value or maximum RCWV listed above, whichever is lower

3. The resistance of jumper is defined <  $0.05\Omega$ 



#### **Dimensions (mm)**

MCSR04	L	W	Т	Tb	Tt
(0402)	1 ±0.05	0.5 ±0.05	0.35 ±0.05	0.25 ±0.1	0.2 ±0.1

#### Marking

Size \ No. of Digit of Code \ Tolerance	±5%	±1%
MCMR12 (1206)	No Marking	

#### **Functional Description**

#### **Product characterization**

Standard values of nominal resistance are taken from the E24 series for resistors with a tolerance of  $\pm 5\%$ , and E24+E96 series for resistors with a tolerance of  $\pm 1\%$ . The values of the E24 / E96 series are in accordance with "IEC publication 60063"








#### **Derating**

The power that the resistor can dissipate depends on the operating temperature



Max. dissipation in percentage of rated power as a function of the ambient temperature

#### Mounting:

Due to their rectangular shapes and small tolerances, surface mountable resistors are suitable for handling by automatic placement systems

Chip placement can be on ceramic substrates and printed-circuit boards (PCBs)


Electrical connection to the circuit is by individual soldering condition

The end terminations guarantee a reliable contact

#### **Soldering Condition**

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260°C for 10 seconds. Therefore, it is possible to mount surface mount resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs)

Surface mount resistors are tested for solderability at 235°C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in below.



Infrared soldering profile for Chip Resistors





#### **Test and Requirements**

Essentially all tests are carried out according to the schedule of IEC publication 115-8, category LCT/UCT/56 (rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days). The testing also meets the requirements specified by EIA, EIAJ and JIS

The tests are carried out in accordance with IEC publication 68, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to IEC 60068-1, subclause 5.3. Unless otherwise specified, the following value supplied:

Temperature : 15°C to 35°C Relative humidity : 45% to 75%

Air pressure : 86kPa to 106kPa (860 mbar to 1,060 mbar) All soldering tests are performed with midly activated flux

Test Procedure / Test Method	Requirement		
Test	Procedure / Test Method	Resistance ±5%, ±1%	0Ω
Electrical Characteristics	- DC resistance values measurement - Temperature Coefficient of Resistance (T.C.R) Natural resistance change per change in degree centigrade	Within the specified tolera	
JISC5201-1: 1998 Clause 4.8	R2 - R1 R1 (t2 - t1) × 10 <sup>6</sup> (ppm/°C) t1 : 20°C +5°C -1°C	Refer to "Quick Reference [	Data"
	R1 : Resistance at reference temperature R2 : Resistance at test temperature		
Resistance to soldering heat (R.S.H) MIL-STD-202 method 210	Un-mounted chips completely immersed for 10 ±1 second in a SAC solder bath at 270°C ±5°C	$\Delta$ R/R Max. ± (0.5%+0.05 $\Omega$ ) No visible damage	< 50mΩ
Solderability J-STD-002	<ul> <li>a) Bake the sample for 155°C dwell time 4 hours / solder dipping 235°C / 5 s</li> <li>b) Steam the sample dwell time 1 hour/ solder dipping 215°C/ 5 s</li> <li>c) Steam the sample dwell time 1 hour/ solder dipping 260°C / 7 s</li> </ul>	95% coverage minimum, good tir No visible damage	nning
Temperature cycling JESD22 method JA-104	1,000 cycles, -55°C to +155°C, dwell time 5 to 10mins	$\Delta$ R/R Max. ± (0.5%+0.05 $\Omega$ ) No visible damage	< 50mΩ
Moisture Resistance MIL-STD-202 method 106	65 ±2°C, 80 to 100% RH, 10 cycles, 24 hours / cycle	$\Delta$ R/R Max. ± (0.5%+0.05 $\Omega$ ) No visible damage	< 50mΩ
Bias Humidity MIL-STD-202 method 103	1,000 +48/-0 hours; 85°C, 85% RH, 10% of operation Power	$\Delta$ R/R Max. ± (1%+0.05Ω) No visible damage	< 50mΩ
Operational Life MIL-STD-202 method 108	1,000 +48/-0 hours; 35% of operation power, 125 ±2°C	$\Delta$ R/R Max. ± (1%+0.05 $\Omega$ ) No visible damage	< 50mΩ
High Temperature Exposure MIL-STD-202 method 108	1,000+48/-0 hours; without load in a temperature chamber controlled 155±3°C	$\Delta$ R/R Max. ± (1%+0.05 Ω) No visible damage	< 50mΩ





#### **Test and Requirements**

Test Procedure / Test Method	Requirement		
Test	Procedure / Test Method	Resistance ±5%, ±1%	0Ω
Mechanical Shock MIL-STD-202 method 213	1/2 sine pulse / 1,500 g peak / Velocity 15.4 ft/s	Within the specified tolerance No visible damage	< 50mΩ
Board Flex AEC-Q200-005	Resistors mounted on a 90 mm glass epoxy resin PCB(FR4), bending once 2 mm for 10 s	$\Delta$ R/R Max. ± (1%+0.05 $\Omega$ ) No visible damage	< 50mΩ
Terminal strength AEC-Q200-006	Pressurizing force: 1 Kg, Test time: 60±1 s	No remarkable damage or remove the terminations	al of
Vibration MIL-STD-202 method 204	Test 5 g's for 20 minimum, 12 cycles each of 3 orientations	$\Delta$ R/R Max. ± (1%+0.05 $\Omega$ ) No visible damage	< 50mΩ
Thermal shock MIL-STD-202 method 107	Test –55 to 155 / dwell time 15 minimum / maximum transfer time 20 seconds 300 cycles	$\Delta$ R/R Max. ± (0.5%+0.05 $\Omega$ ) No visible damage	< 50mΩ
ESD AEC-Q200-002	Test contact 1 KV ( 0.5 KV for 0402 only)	$\Delta$ R/R Max. ± (1%+0.05 $\Omega$ ) No visible damage	< 50mΩ

#### Test Condition for Jumper $(0\Omega)$

Item	MCSR04 (0402)
Power rating at +70°C	1/16 W
Resistance	Max. 50mΩ
Rated current	1A
Peak current	2A
Operating temperature	-55°C to +155°C

#### MCSR04 (0402):

1. Reeled tape packaging : 8 mm width paper taping 10,000 pieces per reel

2. Bulk packaging : 10,000 pieces per poly-bag

#### **Part Number Table**

Description	Part Number
Resistor, 0402, 2R2, 1%, Anti Sulfur	MCSR04W2R20FTL
Resistor, 0402, 0R, Anti Sulfuration	MCSR04X000 PTL
Resistor, 10R, 0402, 5%, Anti Sulfur	MCSR04X100 JTL
Resistor, 0402, 100R, 1%, Anti Sulfur	MCSR04X1000FTL
Resistor, 0402, 1K, 1%, Anti Sulfur	MCSR04X1001FTL
Resistor, 0402, 10K, 1%, Anti Sulfur	MCSR04X1002FTL
Resistor, 0402, 100K, 1%, Anti Sulfur	MCSR04X1003FTL
Resistor, 0402, 1M, 1%, Anti Sulfur	MCSR04X1004FTL

Description	Part Number
Resistor, 100R, 0402, 5%, Anti Sulfur	MCSR04X101 JTL
Resistor, 1K, 0402, 5%, Anti Sulfur	MCSR04X102 JTL
Resistor, 10K, 0402, 5%, Anti Sulfur	MCSR04X103 JTL
Resistor, 100K, 0402, 5%, Anti Sulfur	MCSR04X104 JTL
Resistor, 1M, 0402, 5%, Anti Sulfur	MCSR04X105 JTL
Resistor, 0402, 1K07, 1%, Anti Sulfur	MCSR04X1071FTL
Resistor, 0402, 10R, 1%, Anti Sulfur	MCSR04X10R0FTL
Resistor, 0402, 110R, 1%, Anti Sulfur	MCSR04X1100FTL





Description	Part Number
Resistor, 0402, 1K1, 1%, Anti Sulfur	MCSR04X1101FTL
Resistor, 0402, 11K, 1%, Anti Sulfur	MCSR04X1102FTL
Resistor, 0402, 110K, 1%, Anti Sulfur	MCSR04X1103FTL
Resistor, 0402, 11R, 1%, Anti Sulfur	MCSR04X11R0FTL
Resistor, 0402, 120R, 1%, Anti Sulfur	MCSR04X1200FTL
Resistor, 0402, 1K2, 1%, Anti Sulfur	MCSR04X1201FTL
Resistor, 0402, 12K, 1%, Anti Sulfur	MCSR04X1202FTL
Resistor, 0402, 120K, 1%, Anti Sulfur	MCSR04X1203FTL
Resistor, 0402, 1K21, 1%, Anti Sulfur	MCSR04X1211FTL
Resistor, 0402, 12R, 1%, Anti Sulfur	MCSR04X12R0FTL
Resistor, 0402, 130R, 1%, Anti Sulfur	MCSR04X1300FTL
Resistor, 0402, 1K3, 1%, Anti Sulfur	MCSR04X1301FTL
Resistor, 0402, 13K, 1%, Anti Sulfur	MCSR04X1302FTL
Resistor, 0402, 130K, 1%, Anti Sulfur	MCSR04X1303FTL
Resistor, 0402, 1K33, 1%, Anti Sulfur	MCSR04X1331FTL
Resistor, 0402, 13K3, 1%, Anti Sulfur	MCSR04X1332FTL
Resistor, 0402, 1K37, 1%, Anti Sulfur	MCSR04X1371FTL
Resistor, 0402, 13K7, 1%, Anti Sulfur	MCSR04X1372FTL
Resistor, 0402, 13R, 1%, Anti Sulfur	MCSR04X13R0FTL
Resistor, 0402, 1K4, 1%, Anti Sulfur	MCSR04X1401FTL
Resistor, 0402, 14R, 1%, Anti Sulfur	MCSR04X14R0FTL
Resistor, 0402, 150R, 1%, Anti Sulfur	MCSR04X1500FTL
Resistor, 0402, 1K5, 1%, Anti Sulfur	MCSR04X1501FTL
Resistor, 0402, 15K, 1%, Anti Sulfur	MCSR04X1502FTL
Resistor, 0402, 150K, 1%, Anti Sulfur	MCSR04X1503FTL
Resistor, 0402, 1K54, 1%, Anti Sulfur	MCSR04X1541FTL
Resistor, 0402, 15R, 1%, Anti Sulfur	MCSR04X15R0FTL
Resistor, 0402, 160R, 1%, Anti Sulfur	MCSR04X1600FTL
Resistor, 0402, 1K6, 1%, Anti Sulfur	MCSR04X1601FTL
Resistor, 0402, 16K, 1%, Anti Sulfur	MCSR04X1602FTL
Resistor, 0402, 160K, 1%, Anti Sulfur	MCSR04X1603FTL
Resistor, 0402, 1K65, 1%, Anti Sulfur	MCSR04X1651FTL
Resistor, 0402, 1K69, 1%, Anti Sulfur	MCSR04X1691FTL
Resistor, 0402, 16K9, 1%, Anti Sulfur	MCSR04X1692FTL
Resistor, 0402, 16R, 1%, Anti Sulfur	MCSR04X16R0FTL
Resistor, 0402, 180R, 1%, Anti Sulfur	MCSR04X1800FTL

Description	Part Number
Resistor, 0402, 1K8, 1%, Anti Sulfur	MCSR04X1801FTL
Resistor, 0402, 18K, 1%, Anti Sulfur	MCSR04X1802FTL
Resistor, 0402, 180K, 1%, Anti Sulfur	MCSR04X1803FTL
Resistor, 0402, 187K, 1%, Anti Sulfur	MCSR04X1873FTL
Resistor, 0402, 18R, 1%, Anti Sulfur	MCSR04X18R0FTL
Resistor, 0402, 1K96, 1%, Anti Sulfur	MCSR04X1961FTL
Resistor, 0402, 19K6, 1%, Anti Sulfur	MCSR04X1962FTL
Resistor, 0402, 200R, 1%, Anti Sulfur	MCSR04X2000FTL
Resistor, 0402, 2K, 1%, Anti Sulfur	MCSR04X2001FTL
Resistor, 0402, 20K, 1%, Anti Sulfur	MCSR04X2002FTL
Resistor, 0402, 200K, 1%, Anti Sulfur	MCSR04X2003FTL
Resistor, 200R, 0402, 5%, Anti Sulfur	MCSR04X201 JTL
Resistor, 0402, 2K05, 1%, Anti Sulfur	MCSR04X2051FTL
Resistor, 0402, 20R, 1%, Anti Sulfur	MCSR04X20R0FTL
Resistor, 0402, 2K15, 1%, Anti Sulfur	MCSR04X2151FTL
Resistor, 0402, 220R, 1%, Anti Sulfur	MCSR04X2200FTL
Resistor, 0402, 2K2, 1%, Anti Sulfur	MCSR04X2201FTL
Resistor, 0402, 22K, 1%, Anti Sulfur	MCSR04X2202FTL
Resistor, 0402, 220K, 1%, Anti Sulfur	MCSR04X2203FTL
Resistor, 0402, 22R, 1%, Anti Sulfur	MCSR04X22R0FTL
Resistor, 0402, 23K7, 1%, Anti Sulfur	MCSR04X2372FTL
Resistor, 0402, 240R, 1%, Anti Sulfur	MCSR04X2400FTL
Resistor, 0402, 2K4, 1%, Anti Sulfur	MCSR04X2401FTL
Resistor, 0402, 24K, 1%, Anti Sulfur	MCSR04X2402FTL
Resistor, 0402, 240K, 1%, Anti Sulfur	MCSR04X2403FTL
Resistor, 0402, 2K43, 1%, Anti Sulfur	MCSR04X2431FTL
Resistor, 0402, 24R, 1%, Anti Sulfur	MCSR04X24R0FTL
Resistor, 0402, 2K61, 1%, Anti Sulfur	MCSR04X2611FTL
Resistor, 0402, 270R, 1%, Anti Sulfur	MCSR04X2700FTL
Resistor, 0402, 2K7, 1%, Anti Sulfur	MCSR04X2701FTL
Resistor, 0402, 27K, 1%, Anti Sulfur	MCSR04X2702FTL
Resistor, 0402, 270K, 1%, Anti Sulfur	MCSR04X2703FTL
Resistor, 0402, 2K74, 1%, Anti Sulfur	MCSR04X2741FTL
Resistor, 0402, 27R, 1%, Anti Sulfur	MCSR04X27R0FTL
Resistor, 0402, 300R, 1%, Anti Sulfur	MCSR04X3000FTL
Resistor, 0402, 3K, 1%, Anti Sulfur	MCSR04X3001FTL





Description	Part Number
Resistor, 0402, 30K, 1%, Anti Sulfur	MCSR04X3002FTL
Resistor, 0402, 300K, 1%, Anti Sulfur	MCSR04X3003FTL
Resistor, 0402, 30K1, 1%, Anti Sulfur	MCSR04X3012FTL
Resistor, 300K, 0402, 5%, Anti Sulfur	MCSR04X304 JTL
Resistor, 0402, 30R, 1%, Anti Sulfur	MCSR04X30R0FTL
Resistor, 0402, 330R, 1%, Anti Sulfur	MCSR04X3300FTL
Resistor, 0402, 3K3, 1%, Anti Sulfur	MCSR04X3301FTL
Resistor, 0402, 33K, 1%, Anti Sulfur	MCSR04X3302FTL
Resistor, 0402, 330K, 1%, Anti Sulfur	MCSR04X3303FTL
Resistor, 0402, 3K32, 1%, Anti Sulfur	MCSR04X3321FTL
Resistor, 0402, 33R, 1%, Anti Sulfur	MCSR04X33R0FTL
Resistor, 0402, 340R, 1%, Anti Sulfur	MCSR04X3400FTL
Resistor, 0402, 360R, 1%, Anti Sulfur	MCSR04X3600FTL
Resistor, 0402, 3K6, 1%, Anti Sulfur	MCSR04X3601FTL
Resistor, 0402, 3K6, 1%, Anti Sulfur	MCSR04X3602FTL
Resistor, 0402, 360K, 1%, Anti Sulfur	MCSR04X3603FTL
Resistor, 0402, 3K65, 1%, Anti Sulfur	MCSR04X3651FTL
Resistor, 0402, 36R, 1%, Anti Sulfur	MCSR04X36R0FTL
Resistor, 0402, 3K83, 1%, Anti Sulfur	MCSR04X3831FTL
Resistor, 0402, 390R, 1%, Anti Sulfur	MCSR04X3900FTL
Resistor, 0402, 3K9, 1%, Anti Sulfur	MCSR04X3901FTL
Resistor, 0402, 39K, 1%, Anti Sulfur	MCSR04X3902FTL
Resistor, 0402, 390K, 1%, Anti Sulfur	MCSR04X3903FTL
Resistor, 0402, 3K92, 1%, Anti Sulfur	MCSR04X3921FTL
Resistor, 0402, 39R, 1%, Anti Sulfur	MCSR04X39R0FTL
Resistor, 0402, 4K02, 1%, Anti Sulfur	MCSR04X4021FTL
Resistor, 0402, 430R, 1%, Anti Sulfur	MCSR04X4300FTL
Resistor, 0402, 4K3, 1%, Anti Sulfur	MCSR04X4301FTL
Resistor, 0402, 43K, 1%, Anti Sulfur	MCSR04X4302FTL
Resistor, 0402, 430K, 1%, Anti Sulfur	MCSR04X4303FTL
Resistor, 0402, 432K, 1%, Anti Sulfur	MCSR04X4323FTL
Resistor, 0402, 43R, 1%, Anti Sulfur	MCSR04X43R0FTL
Resistor, 0402, 470R, 1%, Anti Sulfur	MCSR04X4700FTL
Resistor, 0402, 4K7, 1%, Anti Sulfur	MCSR04X4701FTL
Resistor, 0402, 47K, 1%, Anti Sulfur	MCSR04X4702FTL
Resistor, 0402, 470K, 1%, Anti Sulfur	MCSR04X4703FTL

Description	Part Number
Resistor, 4K7, 0402, 5%, Anti Sulfur	MCSR04X472 JTL
Resistor, 0402, 47K5, 1%, Anti Sulfur	MCSR04X4752FTL
Resistor, 0402, 47R, 1%, Anti Sulfur	MCSR04X47R0FTL
Resistor, 0402, 4K87, 1%, Anti Sulfur	MCSR04X4871FTL
Resistor, 0402, 499R, 1%, Anti Sulfur	MCSR04X4990FTL
Resistor, 0402, 4K99, 1%, Anti Sulfur	MCSR04X4991FTL
Resistor, 0402, 49K9, 1%, Anti Sulfur	MCSR04X4992FTL
Resistor, 0402, 49R9, 1%, Anti Sulfur	MCSR04X49R9FTL
Resistor, 0402, 510R, 1%, Anti Sulfur	MCSR04X5100FTL
Resistor, 0402, 5K1, 1%, Anti Sulfur	MCSR04X5101FTL
Resistor, 0402, 51K, 1%, Anti Sulfur	MCSR04X5102FTL
Resistor, 0402, 510K, 1%, Anti Sulfur	MCSR04X5103FTL
Resistor, 0402, 511R, 1%, Anti Sulfur	MCSR04X5110FTL
Resistor, 0402, 5K11, 1%, Anti Sulfur	MCSR04X5111FTL
Resistor, 0402, 51R, 1%, Anti Sulfur	MCSR04X51R0FTL
Resistor, 0402, 523R, 1%, Anti Sulfur	MCSR04X5230FTL
Resistor, 0402, 5K23, 1%, Anti Sulfur	MCSR04X5231FTL
Resistor, 0402, 5K36, 1%, Anti Sulfur	MCSR04X5361FTL
Resistor, 0402, 560R, 1%, Anti Sulfur	MCSR04X5600FTL
Resistor, 0402, 5K6, 1%, Anti Sulfur	MCSR04X5601FTL
Resistor, 0402, 56K, 1%, Anti Sulfur	MCSR04X5602FTL
Resistor, 0402, 560K, 1%, Anti Sulfur	MCSR04X5603FTL
Resistor, 0402, 5K62, 1%, Anti Sulfur	MCSR04X5621FTL
Resistor, 0402, 56R, 1%, Anti Sulfur	MCSR04X56R0FTL
Resistor, 0402, 5K9, 1%, Anti Sulfur	MCSR04X5901FTL
Resistor, 5R1, 0402, 5%, Anti Sulfur	MCSR04X5R1 JTL
Resistor, 0402, 6K04, 1%, Anti Sulfur	MCSR04X6041FTL
Resistor, 0402, 60K4, 1%, Anti Sulfur	MCSR04X6042FTL
Resistor, 0402, 620R, 1%, Anti Sulfur	MCSR04X6200FTL
Resistor, 0402, 6K2, 1%, Anti Sulfur	MCSR04X6201FTL
Resistor, 0402, 62K, 1%, Anti Sulfur	MCSR04X6202FTL
Resistor, 0402, 620K, 1%, Anti Sulfur	MCSR04X6203FTL
Resistor, 0402, 62R, 1%, Anti Sulfur	MCSR04X62R0FTL
Resistor, 0402, 6K49, 1%, Anti Sulfur	MCSR04X6491FTL
Resistor, 0402, 680R, 1%, Anti Sulfur	MCSR04X6800FTL
Resistor, 0402, 6K8, 1%, Anti Sulfur	MCSR04X6801FTL





	<b>5</b> (N )
Description	Part Number
Resistor, 0402, 68K, 1%, Anti Sulfur	MCSR04X6802FTL
Resistor, 0402, 680K, 1%, Anti Sulfur	MCSR04X6803FTL
Resistor, 0402, 68K1, 1%, Anti Sulfur	MCSR04X6812FTL
Resistor, 0402, 68R, 1%, Anti Sulfur	MCSR04X68R0FTL
Resistor, 0402, 71K5, 1%, Anti Sulfur	MCSR04X7152FTL
Resistor, 0402, 750R, 1%, Anti Sulfur	MCSR04X7500FTL
Resistor, 0402, 7K5, 1%, Anti Sulfur	MCSR04X7501FTL
Resistor, 0402, 75K, 1%, Anti Sulfur	MCSR04X7502FTL
Resistor, 0402, 750K, 1%, Anti Sulfur	MCSR04X7503FTL
Resistor, 0402, 75R, 1%, Anti Sulfur	MCSR04X75R0FTL
Resistor, 0402, 7K87, 1%, Anti Sulfur	MCSR04X7871FTL
Resistor, 0402, 820R, 1%, Anti Sulfur	MCSR04X8200FTL
Resistor, 0402, 8K2, 1%, Anti Sulfur	MCSR04X8201FTL
Resistor, 0402, 82K, 1%, Anti Sulfur	MCSR04X8202FTL
Resistor, 0402, 820K, 1%, Anti Sulfur	MCSR04X8203FTL
Resistor, 0402, 82R, 1%, Anti Sulfur	MCSR04X82R0FTL
Resistor, 0402, 8K66, 1%, Anti Sulfur	MCSR04X8661FTL
Resistor, 0402, 909R, 1%, Anti Sulfur	MCSR04X9090FTL
Resistor, 0402, 910R, 1%, Anti Sulfur	MCSR04X9100FTL
Resistor, 0402, 9K1, 1%, Anti Sulfur	MCSR04X9101FTL
Resistor, 0402, 91K, 1%, Anti Sulfur	MCSR04X9102FTL
Resistor, 0402, 910K, 1%, Anti Sulfur	MCSR04X9103FTL
Resistor, 0402, 91R, 1%, Anti Sulfur	MCSR04X91R0FTL
Resistor, 0402, 93K1, 1%, Anti Sulfur	MCSR04X9312FTL

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

