

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010081121](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: KK Header, Vertical, Round Pin, 12 Circuits, Tin (Sn) Plating, Pin Length 19.05mm

Documents:

[3D Model](#) [Packaging Specification 30030001-PK-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0087-001 \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [3003](#)
 Application Board-to-Board, Power, Wire-to-Board
 Overview [KK 508 Connector System](#)
 Product Name KK 508
 UPC 800753744837

Physical

Breakaway No
 Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin Natural
 Durability (mating cycles max) 25
 First Mate / Last Break No
 Flammability 94V-2
 Glow-Wire Capable No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 2.989/g
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 3.94mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Bag
 Pitch - Mating Interface 5.08mm
 Pitch - Termination Interface 5.08mm
 Plating min - Mating 5.080µm
 Plating min - Termination 5.080µm
 Polarized to Mating Part No
 Polarized to PCB No
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating See Product Specification
 Termination Interface: Style Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3003 Series](#)

Mates With

KK Crimp Housing [3001](#)
KK PCB
 Receptacle [3002](#)

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	3003-12A
--------------------	----------

Reference - Drawing Numbers

Packaging Specification	30030001-PK-000
Product Specification	PS-99020-0087-001
Sales Drawing	SDAE-3003-NX

This document was generated on 02/26/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION