


Interrata Adjustable

INTERRATA ADJUSTABLE M IP67 CLEAR 1000LM 830 MB

0049042

Product features

- Round shaped in-ground luminaire with +/-30° adjustable light module, drive-over for pressure loads to 2000kg (20kN), comes with 2m 3x1mm² flying lead and recessing tube, aluminium housing with Stainless steel (SS316) decorative ring and clear glass diffuser, IP67, IK10, Class I, non-dimmable, 1025lm, 13.5W, 76lm/W, CRI80, 30° beam angle, 50000 hrs L70 B50 lumen maintenance, 200mm diameter, 229mm recessing tube height, 2.3kg weight.



PRODUCT OVERVIEW

Product name	INTERRATA ADJUSTABLE M IP67 CLEAR 1000LM 830 MB
Technology	LED
Housing	Aluminium
Mount	Ground recessed
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer
ETIM Class	EC000758
E-number FI	4579505
Warranty	5 years
Fixture luminous flux (lm)	1025
Luminaire efficacy (lm/W)	76
Colour temperature (K)	3000
Colour Code	830
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Beam Angle (°)	30
Photobiological Risk Group	RG1
Total power consumption (W)	13.5
Electrical protection	Class I
Dimmable	No
LED Flickering Rate	Low (6% - 20%)
Housing colour	Stainless steel
IP rating	IP67
IK rating	IK10
Product EAN number	5410288490427

Interrata Adjustable

INTERRATA ADJUSTABLE M IP67 CLEAR 1000LM 830 MB

0049042

DATA TABLE

General data

Product name	INTERRATA ADJUSTABLE M IP67 CLEAR 1000LM 830 MB
Technology	LED
Housing	Aluminium
Mount	Ground recessed
General application	Hospitality, Museums & Galleries, Office, Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC000758
E-number FI	4579505
Warranty	5 years

Optical data

Fixture luminous flux (lm)	1025
Luminaire efficacy (lm/W)	76
Colour temperature (K)	3000
Colour Code	830
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Beam Angle (°)	30
Distribution type	Symmetric
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	13.5
Mains voltage (V)	220-240V
Electrical protection	Class I
Dimmable	No
Drive current (mA)	600
Inrush Current (A)	15
Inrush Duration (µs)	200
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Low (6% - 20%)
Max. Luminaires per 10A C Breaker	50
Max. Luminaires per 13A C Breaker	65
Max. Luminaires per 16A C Breaker	80
Max. Luminaires per 20A C Breaker	100
Max. Luminaires per 10A B Breaker	30
Max. Luminaires per 13A B Breaker	39
Max. Luminaires per 16A B Breaker	48
Max. Luminaires per 20A B Breaker	60

Interrata Adjustable

INTERRATA ADJUSTABLE M IP67 CLEAR 1000LM 830 MB

0049042

