

“Schmiermeister“ pneumatic grease systems

For greases and viscous oils



Application:

For mobile lubrication of equipment and machinery

Execution:

- Pressure ratio 55:1, air pressure min./max.: 6 bar/ 10 bar
- Pump type: Double-acting, displacement volume approx. 600 g/min
- Working/bursting pressure: 400 bar/1600 bar
- Pump output and compressed air connection 1/4"
- Portable: Robust trolley with 2 driving and 2 steering wheels
- For 25 kg drums

Delivery:

Grease pump with pre-conveyor system Pressure reducer/water separator Grease follower cover Steel dust cover with integrated barrel screw joint 4 m safety high-pressure lubrication hose (1600 bar) High-pressure grease gun with 360° swivel joint



Art. no.	56260 110
Brand	SAMOA-HALLBAUER
Manufacturer Part Number	40361
Max. operating pressure	400 bar
Suitable for container contents	25 l
Gross Weight	19.000 kg
Product Group	SIG

EAN

4024937403617