



HF-Regulator II for PL-L lamps

HF-R 255 PL-L EII 220-240V 50/60Hz

High-frequency electronic dimming ballast, using the analog protocol (1-10 V) for PL-L lamps

Product data

• General Characteristics

Interface	1-10V
Application code	EII
Rated Lamptype	PL-L
Rated Number of Lamps	2 piece
Rated Ballast-Lamp Power	55
Line Voltage	220-240 V
Line Frequency	50/60 Hz
Housing	L 360x30x21
Energy Efficiency Index	A1
Lifetime 90% surv.@Tcaselife	50000 hr
Ignition Method	Programmed Start

Battery voltage running lamps	154-276
Overvoltage protection 320Vac	48 hr
Overvoltage protection 350Vac	2 hr
Control input protection	Yes (Basic insulation)
Max ballast on MCB(16A type B)	12 x
Stable lamp operation temp.	- [Not specified]
Crestfactor	1.7 (max) -
Hum and Noise level	Inaudible
Total Harmonic Distortion EUR	4 %

• Operating Characteristics

Automatic restart	Yes
Ignition time	0.2 (max) s
Operating frequency	44 (min), 100 (max) kHz
Mains voltage safety (AC)	-10%/+10%
Mains voltage performance (AC)	-8%/+6%
Inrush current Peak	45 (max) A
Inrush current Width	0.40 ms
Earth leakage current	0.5 (max) mA
Power losses gear	11.7 W
Regulating level power	1%-100%
PowerFactor 100%	0.98 -
output power	
Battery voltage lamp ignition	196 V

• Wiring Characteristics

Conn.type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Conn.type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Conn.type ctrl input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Striplength	8.0-9.0 mm
Dual fixture Master/Slave	- [not specified]
Wcs Control input terminals	0.50-1.00 mm2
Wcs Input terminals	0.50-1.00 mm2
Wcs Output terminals	0.50-1.00 mm2

PHILIPS

HF-Regulator II for PL-L lamps

Wcs auto insertion (ALF/ADS) 0.5 mm²

• Temperature Characteristics

T-ignition 0 (min), 50 (max) C
T-ambient -20 (min), 50 (max) C
T-storage -25 (min), 80 (max) C

• Product Dimensions

Length A1 360 mm
Fixing Hole Distance 350 mm
Length A2
Width B1 30 mm
Height C1 22 mm
Fixing Hole Diameter 4.2 mm
D1

• Approval & Application Chars


EMI 9kHz .. 30 MHz EN 55015
EMI 30 MHz .. 1000MHz EN 55022 level B [Level = Class]
Safety Standard IEC 61347-2-3
Performance Standard IEC 60929
Quality Standard ISO 9000:2000
Environmental Standard ISO 14001

Harmonic current emissions IEC 61000-3-2
EMC Immunity IEC 61547
Vibrations IEC 68-2-6 Fc
Bumps IEC 68-2-29 Eb
Humidity EN 61347-2-3 clause 11
Approval marks ENEC / VDE-EMV
CE marking Yes
Temperature marking 110 [Yes]
Emergency standard IEC 60598-2-22

• Product Data

Order code 913700620266
Full product code 913700620266
Full product name HF-R 255 PL-L EII 220-240V 50/60Hz
Order product name HF-R 255 PL-L EII 220-240V 50/60Hz
Pieces per pack 1
Packing configuration 12
Packs per outerbox 12
Bar code on pack - EAN1 8711500911889
Bar code on outerbox - EAN3 8711500911896
Logistic code(s) - 12NC 913700620266
Net weight per piece 0.320 kg

Dimensional drawing



HF-R 255 PL-L EII 220-240V 50/60Hz

Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
HF-R 255 PL-L EII 220-240V 50/60Hz	360	350	30	22	4.2



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 11
data subject to change