

## ExStik<sup>®</sup> ORP Waterproof Meter


 **Flat surface electrodes provides "On-the-Spot" measurements**  
 With  $\pm 4\text{mV}$  accuracy and high 1mV resolution

### Features:

- Measures ORP from -999 to 999mV
- Automatic electronic self calibration
- Simulated analog bar graph displays change in ORP reading
- Memory stores and recalls 15 readings and saves last calibrated value
- Data validation indicators show user the reading is stabilized
- Large 3-1/2 digit (2000 count) Digital display with bar graph
- Data Hold, Auto shut-off and low battery indication
- Easy to replace electrode module is interchangeable with pH and chlorine ExStik<sup>®</sup> modules; (built in chip automatically recognizes the type of probe plugged in for specific measurements)
- Waterproof (IP57) design floats in water and protects the meter in wet environment
- Complete with meter and electrode, protective sensor cap, sample cup, four 3V CR-2032 batteries, and neckstrap
- Optional weighted base (EX006) holds plastic cup and ExStik<sup>®</sup> meter



Patent Pending



Flat surface Electrodes work in liquids, semi-solids and solids

Optional Weighted base (Model EX006)

### Ordering Information:

- RE300 .....ExStik<sup>®</sup> ORP Meter  
 EX006 .....Weighted base with 5 solution cups  
 EX007 .....Spare sample solution cups (24pk)  
 RE305 .....Spare Probe, ORP  
 PH105 .....Spare pH ExStik<sup>®</sup> Electrode Module  
 PH115 .....Spare Probe, pH, Refillable Reference  
 CL205 .....Spare Probe, Chlorine  
 CA895 .....Carrying Case, Small with Belt Loop  
 EX800 .....ExStik 3-in-1 Kit (Chlorine, pH, Temp)  
 EX900 .....ExStik 4-in-1 Kit (Chlorine, pH, ORP, Temp)

Specifications	
ORP (mV)	999 to 999mV
Resolution	1mV
Accuracy	$\pm 4\text{mV}$
Power	four SR44W button batteries
Dimensions	1.4 x 6.8 x 1.6" (35.6 x 172.7 x 40.6mm)
Weight	3.85oz (110g)