

## Datasheet

Art.No. 83.040.0050.0

Access Point WIENET AP ETH-A

WLAN Access Point in industrial design, Wi-Fi standard IEEE 802.11n/g/b, antenna integrated, 1x Ethernet 10/100BaseT, Web-Server, Operating voltage: 24VDC, Protection rate: IP20, DIN rail mounting, WxHxD: 22.5 x 98.6 x 91.5 mm



Art.No.	83.040.0050.0
EAN	4049088338564
Order unit	1 pieces

## Approvals

### Technical data

#### Allgemein

Operating temperature min.	-5 °C
Operating temperature max.	55 °C
Mounting method	DIN rail (top hat rail) 35 mm
Degree of protection (IP)	IP20
Net weight	93 g
LED status indication	Yes
Housing material	Plastic
Ethernet	Yes
Fast Ethernet	Yes

#### Technical data

Voltage type	DC
--------------	----

#### Supply circuit

Voltage type	DC
Operating voltage min.	9 V
Operating voltage max.	28 V
Power consumption max.	1 W

#### Dimensions

Depth	91.5 mm
Width	22.5 mm
Height	96.5 mm
Weight	93 g

Drawings

101,5  
85,2  
96,5  
77,9  
5,8

22,5  
AP ETH-A

22,5  
AP ETH-A-A

04 - REZ 12/92

www.wieland-electric.com  
eshop.wieland-electric.com

Weitere Angaben siehe KATALOG oder eCatalog.  
Additional data see CATALOG or eCatalog.

polys  Stoffverbot- und Beschränkungen nach WH 5020.010 ist einzuhalten.  
Conformity with Wieland document WH 5020.010 n. (list of prohibited / delectable hazardous substances) to be declared

1. Verwendung First Use: Zeichnung Nr. / Drawing No. T 83.040.0050.0 01K  
2. Ersatzteile, keine modifizierten Bauteile CAD drawings, no modified components allowed

Material / Material: 2016  
Zustand: 24.06.  
Kategorie: Klemmer  
Hersteller: Wieland  
Produktionsjahr: 2016  
Maße in mm / Dimensions in mm

Best. / Part: 042051\_01K.DCD  
Ersatz / Replacement: 101

Benennung / Title: wiernet AP ETH-A / AP ETH-A-A  
Type: wiernet AP ETH-A / AP ETH-A-A  
Teilenummer / Part-No.: 83.040.0050.0  
83.040.0051.0

Wieland  
www.wieland-electric.com

Notes: 101  
Date: 12/2002  
Address: / Revision:

04 - REZ 12/92