

# Neodymium Magnets

## Deep Pots

- Highest strength magnet material available
- Cylindrical magnets in a brass pot. Steel pole pieces
- Pot is an essential part of the magnetic circuit
- Both poles are on one face providing superior grip at contact
- Suitable for gripping and lifting applications
- Ideal for use in positioning jigs and soldering fixtures
- Maximum temperature 80°C



Product No.	Diameter	Height (mm)	Unit of pack	Min. pull (N)
<b>E750NEO</b>	6	20	20	10
<b>E751NEO</b>	8	20	20	25
<b>E752NEO</b>	10	20	20	45
<b>E753NEO</b>	13	20	20	70
<b>E754NEO</b>	16	20	10	150
<b>E755NEO</b>	20	25	5	280
<b>E756NEO</b>	25	35	2	450
<b>E757NEO</b>	32	45	2	700

## Shallow Pots

- Highest strength magnet material available
- Cylindrical magnets in zinc plated mild steel pot
- Pot is an essential part of the magnetic circuit
- Both poles are on one face providing superior grip at contact
- Suitable for gripping and lifting applications
- Ideal for use in positioning jigs and soldering fixtures
- Maximum temperature 80°C



Product No.	Diameter	Height (mm)	Unit of pack	Min. pull (N)
<b>E760NEO</b>	6	4.5	20	5
<b>E761NEO</b>	8	4.5	20	13
<b>E762NEO</b>	10	4.5	20	25
<b>E763NEO</b>	13	4.5	20	60
<b>E764NEO</b>	16	4.5	20	95
<b>E765NEO</b>	20	6	10	140
<b>E766NEO</b>	25	7	10	200
<b>E767NEO</b>	32	7	10	350

# Neodymium Magnets

## Shallow Pots with Thread

- Highest strength magnet material available
- Cylindrical magnets in zinc plated mild steel pot
- Pot is an essential part of the magnetic circuit
- Female thread for easy fixing
- Both poles are on one face providing superior grip at contact
- Suitable for gripping and lifting applications
- Ideal for use in positioning jigs and soldering fixtures
- Maximum temperature 80°C



Product No.	Diameter	Height (ex thread) (mm)	Height (inc. thread) (mm)	Thread	Unit of pack	Min. pull (N)
<b>E770NEO</b>	6	4.5	6	M3		5
<b>E771NEO</b>	8	4.5	6	M3	20	13
<b>E772NEO</b>	10	4.5	6	M3	20	25
<b>E773NEO</b>	13	4.5	6	M3	20	60
<b>E774NEO</b>	16	4.5	8	M4	20	95
<b>E775NEO</b>	20	6	8	M4	10	140
<b>E776NEO</b>	25	7	8	M4	10	200
<b>E777NEO</b>	32	7	10	M5	5	350