


Rear Flanges, Front Flanges

Materials:

Flange: Anodised Aluminium.

Screws: Steel, zinc-plated.

Mounting element at the bearing or end cover.



Ordering Details: e.g.: Product-No. 81000120, Rear and Front Flange for Cylinder Ø 20 mm

| Product No. | Cyl. Ø mm | E1 mm | Ø FB mm | MF mm | R mm | TF mm | UF mm | Weight g |
|-------------|--------------|----------|------------|----------|---------|----------|----------|-------------|
| 810 001 20 | 20 | 36 | 6,6 | 8 | 0* | 55 | 70 | 160 |
| 810 001 32 | 32 | 50 | 7 | 10 | 32 | 64 | 80 | 250 |
| 810 001 40 | 40 | 55 | 9 | 10 | 36 | 72 | 90 | 350 |
| 810 001 50 | 50 | 65 | 9 | 12 | 45 | 90 | 110 | 700 |
| 810 001 63 | 63 | 75 | 9 | 12 | 50 | 100 | 125 | 800 |
| 810 001 80 | 80 | 100 | 12 | 16 | 63 | 126 | 154 | 1350 |

* 2 bores on the centre line at a distance TF.

Foot Plate Mountings


Materials:

Mounting: Steel, zinc-plated.

Screws: Steel, zinc-plated.

Mounting element at the bearing and end cover.

Sold by set (2 brackets und 4 screws).



Ordering Details: e.g.: Product-No. 81000220, Foot Plate Mounting for Cylinder Ø 20 mm

| Product No. per Pair | Cyl. Ø mm | Ø AB mm | AH mm | AO mm | AT mm | AU mm | E mm | TR mm | Weight g |
|-------------------------|--------------|------------|----------|----------|----------|----------|---------|----------|-------------|
| 810 002 20 | 20 | 7 | 27 | 6 | 4 | 16 | 36 | 22 | 30 |
| 810 002 25 | 25 | 7 | 29 | 7 | 4 | 16 | 40 | 26 | 40 |
| 810 002 32 | 32 | 7 | 32 | 8 | 4 | 24 | 48 | 32 | 150 |
| 810 002 40 | 40 | 9 | 36 | 9 | 4 | 28 | 53 | 36 | 180 |
| 810 002 50 | 50 | 9 | 45 | 10 | 5 | 32 | 64 | 45 | 300 |
| 810 002 63 | 63 | 9 | 50 | 12 | 5 | 32 | 74 | 50 | 390 |
| 810 002 80 | 80 | 12 | 63 | 19 | 5 | 41 | 98 | 63 | 800 |


Rear Eye Mountings

Materials:

Mounting: Aluminium, die-cast.

Screws: Steel, zinc-plated.

Mounting element at the end cover.



Ordering Details: e.g.: Product-No. 81000420, Rear Eye Mounting for Cylinder Ø 20 mm

| Product No. | Cyl. Ø mm | Ø CD ^{H9} mm | EW mm | FL mm | L mm | MR mm | R mm | Weight g |
|-------------|--------------|--------------------------|----------|----------|---------|----------|---------|-------------|
| 810 004 20 | 20 | 8 | 15,8 | 20 | 14 | 8 | 22 | 20 |
| 810 004 25 | 25 | 8 | 15,8 | 20 | 14 | 8 | 26 | 30 |
| 810 004 32 | 32 | 10 | 25,8 | 22 | 13 | 9 | 32,5 | 90 |
| 810 004 40 | 40 | 12 | 27,8 | 25 | 16 | 12 | 38 | 110 |
| 810 004 50 | 50 | 12 | 31,7 | 27 | 17 | 12 | 46,5 | 170 |
| 810 004 63 | 63 | 16 | 39,7 | 32 | 22 | 15 | 56,5 | 240 |
| 810 004 80 | 80 | 16 | 49,7 | 36 | 22 | 15 | 72 | 370 |