

SVJC boring bar, offset, HSS positive, right-hand

For face and longitudinal turning with CC indexable insert

ATORN[®]

Application


For face and longitudinal turning with CC indexable insert 80°.

Version

- Precision-made boring bar, **HSS**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



Art. No.	17846 184
ISO name	AH 0608 H SCLC R/L 06
Min. bore diameter	8 mm
Tapered diameter	6 mm
Shaft diameter	8 mm
Clearance length	25 mm
Length	100 mm
Clamping surface height	7 mm
Programming size	4 mm
Suitable for indexable inserts	CC.. 06..
Tool design	Right
DIN	8024

EAN-Code

4050293111019