



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL 6W/10 1FM/10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5 [G5]

Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	222
Chromaticity Coordinate Y (Nom)	210

Operating and Electrical	
Power Consumption	6 W
Lamp Current (Nom)	0.16 A
Voltage (Nom)	42 V

Voltage (Nom)	42 V
---------------	------

Mechanical and Housing	
Bulb Shape	T16 [T 16mm]

Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Full product code	871150026039027
Order product name	Actinic BL TL 6W/10 1FM/10X25CC
Order code	928000501030
Numerator - Quantity Per Pack	1


Actinic BL TL(-K) / TL-D(-K)

Numerator - Packs per outer box	250
Material number (12NC)	928000501030
Full product name	Actinic BL TL 6W/10 1FM/10X25CC


EAN/UPC - Case	8711500260413
----------------	---------------

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 6W/10 1FM/10X25CC	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm



Photometric data



Spectral Power Distribution Colour - Actinic BL TL 6W/10 1FM/10X25CC

