


# RFNA4JCCD Datasheet

## Product Name // N Jack Straight 4 Hole Flange RF Connector

[View Product Page](#)

\* Representative product image only



### // Product Description:

- ⊗ N Jack Straight 4 Hole Flange RF Connector
- ⊗ Maximum Voltage: 500V
- ⊗ Temperature range: -55Å°C to +155Å°C
- ⊗ Frequency range: 0GHz - 18GHz
- ⊗ VSWR:
- ⊗ Dielectric withstanding Voltage: >1500V
- ⊗ Impedance: 50Ohm
- ⊗ Body Material: Stainless Steel Passivation
- ⊗ Contact Material: Beryllium Copper

### // General Information:

Product Display Title:	N Type Series Socket 4 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	N Type Series
Body Length:	20.10mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Dielectric Withstanding Voltage:	>1500V
Durability:	>500 cycles
Flange Mount Length:	12.70mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710 & PEI
Max Operating Temperature:	+155°C
Min Operating Temperature:	-55°C
Mount Hole Distance:	8.60mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Socket Diameter:	0.46mm
Thread Size:	5/8 24UNEF 2A
Voltage Max:	500V
Vswr:	<1.30

### // Product PDF Links

[N Type Series Product Datasheet](#)


Have a question or project enquiry  
you'd like to talk to us about?



[Click Here To Contact Us](#)