

knurl cutter HSSE-PM 30°

for use on knurl cutter tools 19100



Application:


For producing straight knurls in accordance with DIN 82 RAA (in holders with 1 knurl) in steel, stainless steel, non-ferrous metals and cast iron material groups.

Execution:

- HSSE PM 30°, ground tooth flanks, coated

Advantage:

- high degree of precision thanks to ground teeth and good cutting performance, even on hard-to-machine materials
- excellent finish quality and long service life thanks to high-quality HSSE-PM cutting material
- coating for increased service life requirements



Art. no.	19173 312
Brand	QUICK
Manufacturer Part Number	42000083
Knurling wheel diameter	21.5 mm
Partition	1.2 mm
Machining direction	Left
Surface	Coated
Gross Weight	0.010 kg
Product Group	192