

## Electro-hydraulic pump from XC series

Wireless and portable



### Application:

For portable use on single-acting or double-acting cylinders.

### Execution:

- Portable and battery-operated electro-hydraulic pump of the XC series, up to 2 times faster than pneumatically operated pumps.
- Two delivery stages.
- 0.5 HP motor with 28 V lithium ion batteries ensure remarkable speed and operating periods
- Two lithium-ion batteries allow very long operating times, as well as a very short charging time.
- Trigger deactivation prevents accidental startup.
- Pressure relief valve with fine adjustment.
- 3/8 inch NPTF connection.
- Bladder tank can be used in any position and prevents oil from escaping.
- With battery charge indicator.



### Advantage:

- Wireless technology eliminates trip hazards e.g. from power cables and air hoses.
- Short setup and disassembly time.
- Ideal for small to medium-sized cylinders as well as hydraulic tools.
- Convertible with more than 140 Enerpac tools and cylinders.

### Delivery:

1x ENERPAC XC1201ME electrically powered hand pump, wireless and portable

|                                   |                          |
|-----------------------------------|--------------------------|
| <b>Art. no.</b>                   | <b>29705 020</b>         |
| <b>Brand</b>                      | ENERPAC                  |
| <b>Manufacturer Part Number</b>   | XC1202ME                 |
| <b>Model</b>                      | XC1202ME                 |
| <b>Max. pressure</b>              | 700 bar                  |
| <b>Feed quantity without load</b> | 2 l/min                  |
| <b>Feed volume 1. Level</b>       | 0.5 l/min < 140 bar      |
| <b>Feed volume 2. Level</b>       | 0.25 l/min up to 700 bar |
| <b>Battery operating voltage</b>  | 230 V/AC                 |
| <b>Length</b>                     | 462 mm                   |
| <b>Height</b>                     | 295 mm                   |
| <b>Width</b>                      | 208 mm                   |
| <b>Tank contents</b>              | 2 l                      |
| <b>Weight</b>                     | 11 kg                    |
| <b>Gross Weight</b>               | 17.000 kg                |
| <b>Product Group</b>              | 258                      |