

VG EMV GEN 4 (EMC cable gland with clamping cage) VG M32 EMV-4 MS 16-25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration



Produktabbildung

Brass cable gland for shielding against interference frequencies with a screening attenuation of up to 100 dB. Contact with cable shield by means of spring washer.

General ordering data

Type	VG M32 EMV-4 MS 16-25
Order No.	2435180000
Version	VG EMV GEN 4 (EMC cable gland with clamping cage), Cable glands, M 32, 9, OD min. 16 - OD max. 25 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
GTIN (EAN)	4050118446937
Qty.	10 pc(s).

**VG EMV GEN 4 (EMC cable gland with clamping cage)
VG M32 EMV-4 MS 16-25**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Length	62 mm	Length (inches)	2.441 inch
Net weight	0.16 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

Material	Brass, nickel-plated	Cable glands	metric
External thread	M 32	Pitch of thread	1.5 mm
Length of thread	9 mm	AF size 1	40 mm
AF size 2	40 mm	Protection degree	IP66, IP68 - 5 bar (30 min.), IP69K
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Operating temperature range, min.	-40 °C
Operating temperature range, max.	100 °C	Outer cable diameter, min.	16 mm
Outer cable diameter, max.	25 mm	Shield diameter, min.	12 mm
Shield diameter, max.	20 mm	Clamp insert	Polyamide
O-Ring	NBR	Seal insert	CR
Tightening torque	6 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN
Engineering Data	STEP