

The engineer's choice





AC 100 MR

INDEX

1	Gei	eneral	3
2	Ме	echanics	3
	2.1 2.2	GeneralConnections	3
3	Ope	perating Data	5
	3.1 3.2 3.3 3.4 3.5	Electrical Interface - Input Electrical Operating Data Electrical Features Aerodynamics Sound Data	
4	Env	vironment	
	4.1 4.2	GeneralClimatic Requirements	
5	Saf	fety	10
	5.1 5.2	Electrical SafetyApproval Tests	10 10



1 General

Fan type	Fan
Rotating direction looking at rotor	Clockwise
Airflow direction	Air intake over flange
Bearing system	Ball bearing
Mounting position - shaft	Any

2 Mechanics


2.1 General

Width	0 mm	
Height	0 mm	
Depth	130 mm	
Diameter	98 mm	
Mass	0,425 kg	
Housing material	Plastic	
Impeller material	Mixed	

2.2 Connections

Electrical connection	Special design	
Lead wire length	See drawing	
Tolerance		
Tube length	See drawing	
Tolerance		
Wire size (AWG)		
Insulation diameter		
Plug	See drawing	·
Contact	See drawing	





Wire	Color	Operation
1	gray	N
2	brown	L
3	black	BOOST



3 Operating Data

3.1 Electrical Interface - Input

External voltage supply for input and output signals must be SELV conform.

Control input	2 speed via jumper + boost

Features

				Switched life / boost	
				0	1
Characteristics		2 speed	0	2050pm	3150rpm
Cital acteristics			1	1250rpm	3150rpm
	0 = Jump 1 = Jump	er geschlosse er offen / <i>jum</i>	en / jun	nper closed en	
				AC 100 indust fan	
				power supply	
Schematics	N L	(± +24V	spe ed setting
	Munidity control eystem	Igh ewtoh		boost	
	_			galvanic isolation	



3.2 Electrical Operating Data

Measurement conditions:

Normal air density = 1,2 kg/m3; Temperature 23° C +/- 3° C; Motor axis horizontal; warm-up time before measuring 5 minutes (unless otherwise specified). In the intake and outlet area

should not be any solid obstruction within 0,5 m.

 $\Delta p = 0$: I:

corresp. to free air flow (see chapter aerodynamics)

I: corresp. to arithm. mean current value

Features	Condition	Symbol		Val	ues	
Voltage range		U	85 V			265 V
Tolerance		U				
Nominal voltage		U_N		115	230 V	
Frequency		f		50 Hz	/ 60 Hz	
Power consumption	$\Delta p = 0$	Р		3,8	8 W	
Tolerance	$\Delta p = 0$	Г	+- 15 %			
Current			55 mA	55 mA	32 mA	30 mA
consumption	$\Delta p = 0$	I _{RMS}	55 IIIA	33 IIIA	32 IIIA	30 IIIA
Tolerance			+- 15 %	+- 15 %	+- 15 %	+- 15 %
Speed				3.150) 1/min	
	$\Delta p = 0$	n		+- 1	0 %	
Tolerance						

3.3 Electrical Features

Electronic function	Speed-Controlled	
Locked rotor protection	Auto restart	
Electronic function	Spood Controlled	

Electronic function	Speed-Controlled	
Locked rotor protection	Auto restart	



2/28/2019 page 6 of 11

3.4 Aerodynamics

Measurement Measured w

Measured with a double chamber intake rig acc. to DIN EN ISO 5801.

conditions: Normal air density = 1,2 kg/m3; Temperature 23° +/ - 3° ;

In the intake and outlet area should not be any solid obstruction within 0,5 m. Motor shaft

horizontal.

The information is only valid under the specified test conditions and may be changed by the

installation conditions. If there are deviations from the standard test conditions, the

characteristic values must be checked under the installed conditions.

a) Operation condition:

3.150 1/min at free air flow Frequency: 50 Hz Nominal voltage: 230 V

Max. free-air flow ($\Delta p = 0 / \dot{v} = max.$)	91,0 m3/h
Max. static pressure ($\Delta p = \text{max.} / \dot{v} = 0$)	55 Pa


b) Operation condition:

3.150 1/min at free air flow Frequency: 60 Hz Nominal voltage: 115

Max. free-air flow ($\Delta p = 0 / \dot{v} = max.$)	91,0 m3/h
Max. static pressure ($\Delta p = \text{max.} / \dot{v} = 0$)	55 Pa



2/28/2019





3.5 Sound Data

Measurement conditions:

Sound pressure level: 1 meter distance between microphone and the air intake.

Measured in a semianchoic chamber with a background noise level of Lp(A) < 5 dB(A)

For further measurement conditions see chapter aerodynamics.

a) Operation condition:

3.150 1/min at free air flow Frequency: 50 Hz Nominal voltage: 230 V

b) Operation condition:

3.150 1/min at free air flow Frequency: 60 Hz Nominal voltage: 115

4 Environment

4.1 General

Min. permitted ambient temperature TU min.	O C
Max. permitted ambient temperature TU max.	50 ℃
Min. permitted storage temperature TL min.	-20 ℃
Max. permitted storage temperature TL max.	85 ℃
Min. permitted ambient temperature TU min.	0°C
Max. permitted ambient temperature TU max.	50 ℃
Min. permitted storage temperature TL min.	-20 ℃
Max. permitted storage temperature TL max.	30 ℃

4.2 Climatic Requirements

Humidity requirements	humid heat, cyclic; according to DIN EN 60068-2-30, 6 cycle	
Water exposure	Splash water check IPX4; according to DIN EN 60529 VDE 0470, not certified	
Dust requirements	Dust check; according to DIN EN 60068-2-68, 6g/m2d, 1 day	
Salt fog requirements	None	
Humidity requirements	humid temperature, cyclic; according to DIN EN 60068-2-38, 10 cycle and condensation water check; according to DIN EN ISO 6270-2, 14 days	
Water exposure	Splash water check IPX4; according to DIN EN 60529 VDE 0470, not certified	
Dust requirements	Dust check IP5X; according to DIN EN 60529 VDE 0470, not certified	
Salt fog requirements	None	

Permitted application area:

The product is for the use in sheltered rooms with limited controlled temperature. Occasionally condensed water is allowed. Direct exposure to water must be avoided. Saline ambient conditions must be avoided.

Pollution degree 3 (according DIN EN 60664-1)

It occurs conductive pollution or dry non-conductive pollution which becomes conductive due to condensation.



5 Safety

5.1 Electrical Safety

A verification of thermal conditions (normal and abnormal operation) as well as the protection against electric shock, ingress of solid foreign objects and water has to be done in conjuction with the appliance.

Test voltage HV type test	1500 V
Unit test voltage	VAC
Time type test HV	60 s
Insulation resistance	RI > 10 MOhm
Protection class	built-in fan
Test voltage HV type test	1500 V
Unit test voltage	VAC
Time type test HV	1 min
Insulation resistance	RI > 50 MOhm
Protection class	built-in fan

5.2 Approval Tests

CE	EC Declaration of Conformity	Yes
EAC	Eurasian Conformity	Yes
UL	Underwriters Laboratories	No
VDE	Association for Electrical, Electronic and Information Technologies	Yes / Approval acc. to EN 60335 (VDE 0700) - Safety for household and similar electrical appliancesApproval acc. to EN 60335 (VDE 0700) - Safety for household and similar electrical appliances
CSA	Canadian Standards Association	No
CCC	China Compulsory Certification	Not applicable

According to the guidelines on the application of Directive 2006/95/EC, chapter III: Scope of the "low voltage" directive, paragraph: Are "components" included in the scope? the following has to be applied:

However, some types of electrical devices, designed and manufactured for being uses as basic components to be incorporated into other electrical equipment, are such that their safety to a very large extent depends on how they are integrated into the final product and the overall characteristics of the final product. These basic components include electronic and certain other components.

Taking into account these objectives of the "Low Voltage" Directive, such basic components, the safety of which can only, to a very large extend, be assessed taking into account, <u>how</u> they are incorporated and for which a risk assessment cannot be undertaken, then they are <u>not</u> covered as such by the Directive. In particular, they must not be CE marked unless covered by other Community legislation that requires CE marking.



