

CUBE67 I/O EXTENSION MODULE


4 analog outputs (U)

Expansion module
AO4 - (E) 4xM12 (U)
Voltage

Housing fully potted. For connection cables please see chapter "Connection Technology"

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Internal communication

Current consumption	max. 50 mA
LED display	US: sensor supply and internal supply voltage (green: OK); UA: actuator supply (green: OK)

Connections

Fieldbus	via internal system connection
----------	--------------------------------

Sensor-system/actuator supply	via internal system connection (max. 2×4 A)
-------------------------------	---

I/O ports	M12 (male) 5-pole, A-coded
-----------	----------------------------

General data

Protection	IP67
------------	------

Mounting method	2-hole screw mounting
-----------------	-----------------------

Temperature range	0...+55 °C (storage temperature -20...+75 °C)
-------------------	---

Dimensions H × W × D	150×30×34.5 mm
----------------------	----------------

Voltage output signals

Load	min. 500 Ohm
------	--------------

Input range	±10 V DC, 0...10 V DC
-------------	-----------------------

Output

Supply voltage	24 V DC (EN 61131-2), via system connection (max. 4 A)
----------------	--

Conversion time (analog)	approx. 1 ms (per channel)
--------------------------	----------------------------

Actuator supply UA	24 V DC (EN 61131-2), max. 1.6 A per M12 female, (short-circuit and overload protected)
--------------------	---

Resolution (analog)	11 Bit + sign
---------------------	---------------

Accuracy	max. ±0.5 % (of range limit)
----------	------------------------------

Diagnostic

Communication status	via LED
----------------------	---------

Diagnostic via LED	per module and channel
--------------------	------------------------

Diagnostic via BUS	per module and channel
--------------------	------------------------

Monitoring - under voltage	yes
----------------------------	-----

Monitoring - no voltage	yes
-------------------------	-----

Short circuit and overload	yes
----------------------------	-----

Actuator warning	per channel via LED and BUS
------------------	-----------------------------

Wire break upper/lower limit overload	per channel via LED and BUS
---------------------------------------	-----------------------------

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85176200
-----------------------	----------

minimum order quantity	1
------------------------	---