

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name

edding ink (Sweet Mint 088) contain in: edding 1200

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Ink for use in felt pens

Uses advised against

No data available.

1.3 Details of the supplier of the safety data sheet

Address

edding International GmbH

Bookkoppel 7

D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

Information provided by / telephone

+49 (0)4102 - 808-0

Advice on Safety Data Sheet

sdb_info@umco.de

1.4 Emergency telephone number

For medical advice (in German and English):

+49 (0)30 30686 790 (Giftnotruf Berlin)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification information

This product does not meet the classification and labelling criteria given in the Regulation (EC) No 1272/2008 (CLP).

2.2 Label elements

Not relevant

Labelling information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

2.3 Other hazards

No data available.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable. The product is not a substance.

3.2 Mixtures

Chemical characterization

Mixture (preparation)

Hazardous ingredients

No	Substance name	Additional information	
	CAS / EC / Index / REACH no	Classification (EC) 1272/2008 (CLP)	Concentration %

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

1	hydrogen [4-[[4-(diethylamino)phenyl][4-[ethyl(3-sulphonatobenzyl)amino]phenyl]methylene]cyclohexa-2,5-dien-1-ylidene](ethyl)(3-sulphonatobenzyl)ammonium, sodium salt C.I. Acid Violet 17			
	4129-84-4 223-942-6 - -	Aquatic Chronic 2; H411	< 2.50	wt%

Full Text for all H-phrases and EUH-phrases: pls. see section 16

3.3 Other information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

In case of persisting adverse effects, consult a physician. Remove contaminated clothing and shoes and launder thoroughly before reusing.

After inhalation

Ensure supply of fresh air.

After skin contact

When in contact with the skin, clean with soap and water.

After eye contact

Remove contact lenses. Rinse eye thoroughly under running water keeping eyelids wide open and protecting the unaffected eye (at least 10 to 15 minutes). Seek medical assistance.

After ingestion

Rinse the mouth thoroughly with water. Call a doctor immediately. Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

No data available.

4.3 Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Extinguishing measures to suit surroundings.

Unsuitable extinguishing media

No data available.

5.2 Special hazards arising from the substance or mixture

None known.

5.3 Advice for firefighters

Use self-contained breathing apparatus. Wear protective clothing.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing.

For emergency responders

No data available. Personal protective equipment (PPE) - see Section 8.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater. Do not discharge into the subsoil/soil.

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

6.3 Methods and material for containment and cleaning up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). When collected, handle material as described under the section heading "Disposal considerations".

6.4 Reference to other sections

No data available.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

Provide good ventilation at the work area (local exhaust ventilation, if necessary). Observe the usual precautions for handling chemicals.

General protective and hygiene measures

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Wash hands before breaks and after work.

Advice on protection against fire and explosion

No special measures necessary.

7.2 Conditions for safe storage, including any incompatibilities

Technical measures and storage conditions

Keep container tightly closed and dry in a cool, well-ventilated place.

Requirements for storage rooms and vessels

Store product in closed containers.

Incompatible products

None known

7.3 Specific end use(s)

No data available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

No parameters available for monitoring.

8.2 Exposure controls

Appropriate engineering controls

No data available.

Personal protective equipment

Respiratory protection

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

Eye / face protection

Safety glasses (EN 166)

Hand protection

In case of intensive contact, wear protective gloves (EN 374). Before use, the protective gloves should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Other

Normal chemical work clothing.

Environmental exposure controls

No data available.

SECTION 9: Physical and chemical properties

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

9.1 Information on basic physical and chemical properties

State of aggregation		
liquid		
Form/Colour		
pastel green		
Odour		
characteristic		
pH value		
No data available		
Boiling point / boiling range		
Value	90	°C
Melting point/freezing point		
No data available		
Decomposition temperature		
No data available		
Flash point		
Value	> 93	°C
Ignition temperature		
Value	400	°C
Auto-ignition temperature		
Comments	Product is not selfigniting.	
Flammability		
No data available		
Lower explosion limit		
No data available		
Upper explosion limit		
No data available		
Vapour pressure		
Value	23	hPa
Reference temperature	20	°C
Relative vapour density		
No data available		
Relative density		
No data available		
Density		
Value	1	g/cm ³
Reference temperature	20	°C
Solubility in water		
Comments	Completely miscible	
Solubility		
No data available		
Partition coefficient n-octanol/water (log value)		
No data available		
Kinematic viscosity		
No data available		
Solvent content		
Value	13.9	%

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

Solids content	
Value	33.1 %

Particle characteristics	
No data available	

9.2 Other information

Other information	
No data available.	

SECTION 10: Stability and reactivity

10.1 Reactivity

No data available.

10.2 Chemical stability

Stable under recommended storage and handling conditions (See section 7).

10.3 Possibility of hazardous reactions

No data available.

10.4 Conditions to avoid

No data available.

10.5 Incompatible materials

None known.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity	No data available
Acute dermal toxicity	No data available
Acute inhalational toxicity	No data available
Skin corrosion/irritation	No data available
Serious eye damage/irritation	No data available
Respiratory or skin sensitisation	No data available
Germ cell mutagenicity	No data available
Reproduction toxicity	No data available
Carcinogenicity	No data available
STOT - single exposure	No data available
STOT - repeated exposure	No data available

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

Aspiration hazard
No data available

11.2 Information on other hazards

Endocrine disrupting properties

No data available.

Other information

No data available.

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish (acute)
No data available

Toxicity to fish (chronic)
No data available

Toxicity to Daphnia (acute)
No data available

Toxicity to Daphnia (chronic)
No data available

Toxicity to algae (acute)
No data available

Toxicity to algae (chronic)
No data available

Bacteria toxicity
No data available

12.2 Persistence and degradability

No data available.

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

No data available.

12.5 Results of PBT and vPvB assessment

No data available.

12.6 Endocrine disrupting properties

No data available.

12.7 Other adverse effects

No data available.

12.8 Other information

Other information
Do not discharge product unmonitored into the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

Residues must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

SECTION 14: Transport information

14.1 Transport ADR/RID/ADN

The product is not subject to ADR/RID/ADN regulations.

14.2 Transport IMDG

The product is not subject to IMDG regulations.

14.3 Transport ICAO-TI / IATA

The product is not subject to ICAO-TI / IATA regulations.

14.4 Other information

No data available.

14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

14.6 Special precautions for user

No data available.

14.7 Maritime transport in bulk according to IMO instruments

Not relevant

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

REACH candidate list of substances of very high concern (SVHC) for authorisation

According to available data and the information provided by preliminary suppliers, the product does not contain substances that are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, MIXTURES AND ARTICLES

The product contains following substance(s) that are considered being subject to REACH regulation (EC) 1907/2006 annex XVII.

No	Substance name	CAS no.	EC no.	No
1	hydrogen [4-[[4-(diethylamino)phenyl][4-ethyl(3-sulphonatobenzyl)amino]phenyl]methylene]cyclohexa-2,5-dien-1 ylidene](ethyl)(3-sulphonatobenzyl)ammonium, sodium salt C.I. Acid Violet 17	4129-84-4	223-942-6	75

Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances

This product is not subject to Part 1 or 2 of Annex I.

15.2 Chemical safety assessment

A chemical safety assessment has not been carried out for this mixture.

SECTION 16: Other information

Sources of key data used to compile the data sheet:

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.
Directives 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164.

Trade name: edding ink (Sweet Mint 088) contain in: edding 1200

Current version : 1.0.0, issued: 25.04.2022

Replaced version: -, issued: -

Region: GB

National Threshold Limit Values of the corresponding countries as amended in each case.
Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.
The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding section.

Full text of the H- and EUH- phrases drawn up in sections 2 and 3 (provided not already drawn up in these sections)

H411 Toxic to aquatic life with long lasting effects.

Creation of the safety data sheet

UMCO GmbH
Georg-Wilhelm-Str. 187, D-21107 Hamburg
Tel.: +49 40 / 555 546 300 Fax: +49 40 / 555 546 357 e-mail: umco@umco.de

This information is based on our present knowledge and experience.
The safety data sheet describes products with a view to safety requirements.
It does not however, constitute a guarantee for any specific product properties and shall not establish a legally valid contractual relationship.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO GmbH.
Prod-ID 757553