

SC Torus multi-tooth mills

6-10 cutting edges with RockTec PRO coating

ATORN[®]



Application

Torus multi-tooth mills in long design for machining materials up to 65 HRC, e.g. in die and mould making.

Version

- Cutting material, Ultra Micro fine grain
- cutting edge finish
- HA shaft in line with DIN 6535
- Clearance
- type H
- With RockTec PRO coating
- Radius tolerance = +/- 0.005 mm

Advantage

- optimum chip removal and temperature resistance
- Optimised geometry for machining hard materials
- maximum service life thanks to RockTec PRO coating

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.		
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC	
			130																145	

Art. No.	16952 708
Cutting material	VHM
Surface	TiAlSiN
Type	H
Number of cutting edges	6 PCS
Twist angle	45°
Tool holding device	HA parallel shank
Overall length	Long
Cutting edge diameter	4 mm
Cutting edge length	12 mm
Length	65 mm
Shaft diameter	6 mm
Edge radius	1 mm
fz hard 65 HRC	0.035 mm

EAN-Code

4050293652635