

SDQC offset steel boring bar, positive, right

for longitudinal and copy turning with DC indexable insert in holder

ATORN[®]



Application

For longitudinal and copy turning with DC 55° indexable insert.

Version

- precision-manufactured steel boring bar, with inner cooling, offset, D type, 107.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage

- slim contour, optimised for copy turning work
- positive body geometry ensures low cutting forces

Art. no.	17827 673
ISO name	E0406-SDQC R/L 04-AX
Min. bore diameter	5.2 mm
Shaft diameter	6 mm
Clearance length	26 mm
Length	56 mm
Programming size	2.6 mm
Plate height	1.1 mm
Suitable for indexable inserts	DC.. 04..
Tool design	Right

EAN-Code

4050293562200