

INCREM. ENCODER WITH RS 422 (TTL), 3600 P/R, CLAMP
FLANGE WELLE 10 MM OPERATING VOLTAGE 5 V AXIAL
FLANGE CONNECTOR



Figure similar

product brand name	Measuring systems
Design of the interface	TTL / RS 422
Measuring procedure / for position feedback	Incremental
Operating voltage / of the rotary encoder / for DC	5 V
Relative symmetrical tolerance / of the operating voltage / of the rotary encoder / for DC	10 %
Scanning frequency / maximum	300 kHz
Consumed current / without load / maximum	150 mA
Standard for interfaces	TTL (RS 422)
Property of the output / Short-circuit proof against 0 V	Yes
Pulse duration / with 1 m connecting cable / with recommended input circuit / maximum / Note	Rise / fall time $t_{+}/t_{-} \leq$
Pulse duration / with 1 m connecting cable / with recommended input circuit / maximum	50 ns
Phase displacement angle / between signal A and signal B	90°
Edge interval / between signal A and signal B <ul style="list-style-type: none"> • with scanning frequency 300 kHz / minimum 	0.45 μ s
Cable length <ul style="list-style-type: none"> • maximum 	100 m
Failure monitoring type / for LED	High impedance driver
Incremental resolution <ul style="list-style-type: none"> • per revolution / maximum 	3 600
Measurement deviation angle of rotation / of the incremental encoder	18"
Speed	

<ul style="list-style-type: none"> • with electrical rotation transmission / maximum • maximum 	5 000 1/min 12 000 1/min
Friction torque / at 20 °C / maximum	0.01 N·m
Starting torque / at 20 °C / maximum	0.01 N·m
Axial force / at shaft <ul style="list-style-type: none"> • with $n \leq 6000$ rpm / maximum • with $n > 6000$ rpm / maximum 	40 N 10 N
Cantilever force / at shaft extension <ul style="list-style-type: none"> • with $n \leq 6000$ rpm / maximum • with $n > 6000$ rpm / maximum 	60 N 20 N
Outer diameter / of rotary encoder shaft	10 mm
Length / of rotary encoder shaft	20 mm
Angular acceleration / maximum	100 000 rad/s ²
Moment of inertia / of rotor	0.0000015 kg·m ²
Resistance against vibration / at 55 Hz ... 2 kHz / acc. to IEC 60068-2-6	300 m/s ²
Shock acceleration <ul style="list-style-type: none"> • limited to 2 ms / acc. to IEC 60068-2-27 • limited to 6 ms / acc. to IEC 60068-2-27 	2 000 m/s ² 1 000 m/s ²
Protection class IP <ul style="list-style-type: none"> • without shaft input • with shaft input 	IP67 IP64
Ambient temperature <ul style="list-style-type: none"> • with supply voltage $5\text{ V} \pm 10\%$ / with installed cable / during operation • with supply voltage $5\text{ V} \pm 10\%$ / with moving cable / during operation 	-40 ... +100 -10 ... +100
Net weight	0.3 kg
EMI immunity	Tested according to the EMC guidelines 89/336/EEC and the rules of the EMC guidelines (generic standards)
Certificate of suitability	CE, cULus
Flange type	Clamping flange
Direction of connection opening	Axial
Type of electrical connection	Flange socket

Further information

Information und Download Center

https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx

Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catagog/Product/6FX20012RD60/all>

Industry Online Support

<http://support.automation.siemens.com/WW/view/en/6FX20012RD60/all>

last modified:

09.03.2015