



# EcoLED T8

T8 ECOLED STD 1500MM G1324W840

This T8 tube is the ideal product for quickly and economically converting fluorescent tube luminaires to the new LED technology. With a small technical intervention you will thus have extremely energy-saving luminaires.

**Order code 56234**

**EAN 8002219736529**

## Technical specifications

Absorbed Power	<b>24 W</b>
Lampholder	<b>G13</b>
Supply voltage type	<b>AC</b>
Nominal voltage (AC)	<b>230 Vac</b>
Ambient temperature (min)	<b>-20 °C</b>
Ambient temperature (max)	<b>40 °C</b>
CCT light tone	<b>4000 K</b>
Photobiological risk	<b>RG0</b>
Beam angle	<b>180 °</b>
Bulb shape	<b>Other</b>
Colour consistency	<b>SDCM6</b>
Consumption (1000h)	<b>24 KWh</b>
CRI color rendering	<b>&gt;80</b>
Diameter	<b>28 mm</b>
Efficiency	<b>104 lm/W</b>
Energy class	<b>F</b>
Eprel code	<b>562929</b>
Equivalent power	<b>58W</b>
Frequency (max)	<b>60 Hz</b>
Frequency (min)	<b>50 Hz</b>
Power factor	<b>0.51</b>
Life	<b>15000 h</b>
Lighting Sources Flux	<b>2500 lm</b>
Luminous flux L70B50	<b>15000 h</b>
Switching cycles	<b>8000</b>
Voltage supply range (max)	<b>240 V</b>
Voltage supply range (min)	<b>220 V</b>

## Mechanical specifications

Height	<b>1513 mm</b>
Diffuser finiture	<b>Frosted</b>
Protection grade IP	<b>IP20</b>

## Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN 62776:2015, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013, REG. 2019/2020(EU)

