




## Inductive NAMUR sensor

IG-2005-N/6M/1D/1G/2G



Product characteristics	
Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	5
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 33
Electrical data	
Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...30; (when used outside the hazardous area)
Current consumption [mA]	< 1; (disabled; conductive: > 2,1)
Protection class	II
Outputs	
Electrical design	NAMUR
Output function	normally closed
Permanent current rating of switching output DC [mA]	30; (when used outside the hazardous area)
Switching frequency DC [Hz]	720
Detection zone	
Sensing range [mm]	5
Real sensing range Sr [mm]	5 ± 10 %
Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-10...10
Operating conditions	
Ambient temperature [°C]	-20...80
Protection	IP 67

# NG5019



## Inductive NAMUR sensor

IG-2005-N/6M/1D/1G/2G

Tests / approvals	
Approval	PTB 01 ATEX 2191; BVS 04 ATEX E153; TIIS TC16108; IECEx BVS 06.0003
ATEX marking	$\text{Ex}$ II 1G Ex ia IIB T6 Ga
	$\text{Ex}$ II 2G Ex ia IIC T6 Gb
	$\text{Ex}$ II 1D Ex ia IIIC T 90°C Da
EMC	EN 60947-5-6
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)
MTTF [years]	4697

Safety classification	
Max. internal capacitance [nF]	146
Max. internal inductance [ $\mu$ H]	49


Mechanical data	
Weight [g]	314.4
Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M18 x 1 / L = 33
Thread designation	M18 x 1
Materials	PBT

Accessories	
Accessories (supplied)	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 6 m, PVC; 2 x 0.5 mm <sup>2</sup>	

### Connection



Core colours :  
BN = brown  
BU = blue