

Precision short drill chucks



Application:


For clamping tools with straight shank.

Version:

- For NC lathes
- The tool is clamped using a hexagon key
- Hexagon T-handle wrench operation

Advantage:

- High concentricity



Art. no.	22725 046
VDI mount diameter	40 mm
Min./max. clamping width	2.5-16 mm
Outer diameter	56 mm
Discharge length, open	100 mm
Discharge length, closed	95 mm