

Model Number

OBE20M-R100-S2EP-IO-V31-L

Laser thru-beam sensor with 4-pin, M8 x 1 connector

Features

- Miniature design with versatile moun-• ting options
- DuraBeam Laser Sensors durable ٠ and employable like an LED
- IO-link interface for service and pro-• cess data
- Various frequencies for avoiding mutual interference (cross-talk immunity)
- Extended temperature range -40°C ... 60°C
- High degree of protection IP69K ٠

Product information


The R100 series miniature optical sensors are the first devices of their kind to offer an end-to-end solution in a small single standard design - from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link.


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.


Dimensions



Electrical connection emitter



Electrical connection receiver



Pinout





Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



LASER PRODUCT IEC 60825-1: 2007 certified.

Accessories V31-WM-2M-PUR

V31-GM-2M-PUR

IO-Link-Master02-USB

plug for sensor connection

www.pepperl-fuchs.com

Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Female cordset, M8, 4-pin, PUR cable

Female cordset, M8, 4-pin, PUR cable

IO-Link master, supply via USB port or separate power supply, LED indicators, M12

Other suitable accessories can be found at

Indicators/operating means Laserlabel Emitter 1 Operating indicator CLASS 1 T I ASER 1 PRODUCT **T** Receiver 1 2 Light-on/Dark-on changeover switch 1 CLASS 1 2 Sensitivity adjuster LASER PRODUCT З Ø Ø 3 Operating indicator / dark on **H** IEC 60825-1: 2007 certified. (\mathbf{P}) 4 4 Signal indicator Complies with 21 CFR 1040.10 and 1040.11 except 5 Operating indicator / light on for deviations pursuant to Laser Notice No. 50, dated June 24, 2007 5 CLASS 1

Release date: 2016-06-09 15:15 Date of issue: 2016-06-09 281004_eng.xml

2



Technical data		
System components		
Emitter		OBE20M-R100-S-IO-V31-L
Receiver		OBE20M-R100-2EP-IO-V31-L
General specifications		
Effective detection range		0 20 m
Threshold detection range		30 m
Light source		laser diode
Light type		modulated visible red light
Laser nominal ratings		
Note Laser class		LASER LIGHT , DO NOT STARE INTO BEAM
Wave length		680 nm
Beam divergence		> 5 mrad ; d63 < 2 mm in the range 250 750 mm
Pulse length		1.6 μs
Repetition rate		max. 17.6 kHz
max. pulse energy		9.6 nJ
Diameter of the light spot		approx. 50 mm at a distance of 20 m
Angle of divergence		approx. 0.3 °
Ambient light limit		EN 60947-5-2 : 30000 Lux
Functional safety related param	eters	
MTTF _d		440 a
Mission Time (T _M) Diagnostic Coverage (DC)		20 a 0 %
Indicators/operating means		0.70
Operation indicator		LED green:
operation indicator		constantly on - power on
		flashing (4Hz) - short circuit
Function indicator		flashing with short break (1 Hz) - IO-Link mode Yellow LED:
Function indicator		Permanently lit—light path clear
		Permanently off-object detected
		Flashing (4 Hz)—operating reserve not reached
Control elements		Receiver: light/dark switch
Control elements Parameterization indicator		Receiver: sensitivity adjustment IO link communication: green LED goes out briefly (1 Hz)
		to link communication. green LED goes out bheny (1112)
Electrical specifications Operating voltage	UB	10 30 V DC
Ripple	чB	max. 10 %
No-load supply current	I ₀	Emitter: ≤ 13 mA
	0	Receiver: ≤ 13 mA at 24 V supply voltage
Protection class		III
Interface		
Interface type		IO-Link (via $C/Q = pin 4$)
Transfer rate IO-Link Revision		COM 2 (38.4 kBaud) 1.1
Min. cycle time		2.3 ms
Process data witdh		Emitter:
		Process data output: 2 Bit
		Receiver: Process data input: 2 Bit
		Process data output: 2 Bit
SIO mode support		yes
Device ID		Emitter: 0x110402 (1115138)
6		Reciever: 0x110302 (1114882)
Compatible master port type		A
Input Test input		emitter depetivation at 11
Test input		emitter deactivation at +UB
Output Switching type		The switching type of the sensor is adjustable. The default set-
Switching type		ting is:
		C/Q - Pin4: NPN normally open / dark-on, PNP normally closed /
		light-on, IO-Link /Q - Pin2: NPN normally closed / light-on, PNP normally open /
		dark-on
Signal output		2 push-pull (4 in 1)outputs, short-circuit protected, reverse pola-
Outlinhing II		rity protected, overvoltage protected
Switching voltage Switching current		max. 30 V DC max. 100 mA , resistive load
Usage category		DC-12 and DC-13
Voltage drop	U _d	≤ 1.5 V DC
Switching frequency	f	1250 Hz
Response time		0.4 ms
Ambient conditions		
Ambient temperature		-40 60 °C (-40 140 °F)
Storogo tomo sectore		
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		

Refer to "General Notes Relating to PepperI+Fuchs Product Information". Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com





Laser thru-beam sensor		0
Degree of protection	IP67 / IP69 / IP69K	
Connection	M8 x 1 connector, 4-pin	
Material		
Housing	PC (Polycarbonate)	
Optical face	РММА	
Mass	Emitter: approx. 10 g receiver: approx. 10 g	
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC	EN 60947-5-2:2007+A1:2012	
Standard conformity		
Product standard	EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012	
Standards	UL 60947-5-2: 2014 IEC 61131-9:2013 IEC 60825-1:2007 EN 60825-1:2007 EN 61131-9:2013	

Approvals and certificates

UL approval FDA approval E87056 , cULus Listed , class 2 power supply , type rating 1 IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Curves/Diagrams






4



Functions and Operation



- 1 Light-on / dark-on changeover switch 2 - Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range /sensitivity adjuster for more than 180 degrees.

Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on /dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings

Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range /sensitivity adjuster for more than 180 degrees.

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

