

# SUNON

## SPECIFICATION FOR APPROVAL

**CUSTOMER** :  
**DESCRIPTION** : **DC BRUSHLESS FAN**  
**DIMENSIONS** : **120X120X25 mm**  
**M O D E L** : **PMD2412PTB1-A**  
**P/N** : **(2).GN**  
**SUNON SPEC. NO.** : **D12006070G-00**  
**CUSTOMER** :  
**APPROVAL NO.** :  
**APPROVED BY** :  
**CUSTOMER** :  
(AUTHORIZED)

|              |               |                |                |                 |       |                      |                      |
|--------------|---------------|----------------|----------------|-----------------|-------|----------------------|----------------------|
| <b>DRAWN</b> | Ruby<br>07/18 | <b>CHECKED</b> | Kiddy<br>March | <b>APPROVED</b> | Jacky | <b>SPEC.NO</b>       | <b>D12006070G-00</b> |
|              |               |                |                |                 |       | <b>ISSUE DATE</b>    | <b>11.28.2005</b>    |
|              |               |                |                |                 |       | <b>EDITION</b>       | <b>3</b>             |
|              |               |                |                |                 |       | <b>REVISION DATE</b> | <b>07.18.2013</b>    |
|              |               |                |                |                 |       | <b>E.SPEC</b>        | <b>EN12019</b>       |

建準電機工業股份有限公司

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

NO. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888

KAOHSIUNG CITY 80673, TAIWAN (R.O.C)

FAX:886-7-8230505/8230606/8231010

URL:<http://www.sunon.com>

E-mail: [sunon@email.sunon.com.tw](mailto:sunon@email.sunon.com.tw)

2013.07.23

發行章

**DC BRUSHLESS FAN**  
**MODEL : PMD2412PTB1-A**  
**P/N : (2).GN**

**CHARACTERISTICS**

- 1. Motor Design** : DC brushless 4 pole motor design.
- 2. Insulation Resistance** : More than 10M ohm between internal stator and lead wire(+) measured at DC 500V.
- 3. Dielectric Strength** : Applied AC 500V for one minute or AC 600V for 2 seconds between housing and lead wire(+)
- 4. Noise Level** : Measured in a semi-anechoic chamber with background noise level below 15 dB(A). The fan is running in free air with the microphone at a distance of one meter from the fan intake.
- 5. Input Power, Current & Speed** : Measured after continuous 10 minute operation at rated voltage in clean air, and at ambient temperature of 25 degrees C.
- 6. Tolerance** :  $\pm 15\%$  on rated power and current.
- 7. Air Performance** : Measured by a double chamber. The values are recorded when the fan speed has stabilized at rated voltage.

|  |                   |                      |                      |                     |
|--|-------------------|----------------------|----------------------|---------------------|
| 建準電機工業股份有限公司<br>SUNONWEALTH ELECTRIC<br>MACHINE INDUSTRY CO., LTD. | <b>SPEC.NO</b>    | <b>D12006070G-00</b> | <b>REVISION DATE</b> | <b>07. 18. 2013</b> |
|  | <b>ISSUE DATE</b> | <b>11. 28. 2005</b>  | <b>E D I T I O N</b> | <b>3</b>            |
|  | <b>P A G E</b>    | <b>2 O F 9</b>       |                      |                     |

2013.07.23

發行章

|                       |
|-----------------------|
| <b>SPECIFICATIONS</b> |
|-----------------------|

**MODEL : PMD2412PTB1-A****P/N : (2).GN**

- 1-1. Rated Voltage : 24 VDC
- 1-2. Operating Voltage Range : 10~27.6 VDC
- 1-3. Starting Voltage : 10 VDC (25 deg. C POWER ON/OFF)
- 1-4. Rated Speed : 4500 RPM  $\pm$  10%
- 1-5. Air Delivery : 150 CFM
- 1-6. Static Pressure : 0.62 Inch-H<sub>2</sub>O
- 1-7. Rated Current : 490 mA
- 1-8. Rated Power : 11.8 WATTS
- 1-9. Noise Level : 54 dB(A)
- 1-10. Direction of Rotation : Counter-clockwise viewed from front of fan blade
- 1-11. Operating Temperature : -10 to +70 deg. C
- 1-12. Storage Temperature : -40 to +70 deg. C
- 1-13. Bearing System : Precision ball bearing system
- 1-14. Weight : 220 g
- 1-15. Safety : UL/CUR/TUV/CE Approvals
- 1-16. Protection :  Automatic Restart Capability

Note: In a situation where the fan is locked by an external force while the electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is released.

Polarity Protection

|  |            |               |               |              |
|--|------------|---------------|---------------|--------------|
| 建準電機工業股份有限公司<br>SUNONWEALTH ELECTRIC<br>MACHINE INDUSTRY CO., LTD. | SPEC.NO    | D12006070G-00 | REVISION DATE | 07. 18. 2013 |
|  | ISSUE DATE | 11. 28. 2005  | E D I T I O N | 3            |
|  | P A G E    | 3 O F 9       |               |              |

2013.07.23


發行章

**MODEL : PMD2412PTB1-A**

**P/N : (2).GN**

**PERFORMANCE CURVES**

**STATIC  
PRESSURE**



建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD.

|            |               |               |              |
|------------|---------------|---------------|--------------|
| SPEC.NO    | D12006070G-00 | REVISION DATE | 07. 18. 2013 |
| ISSUE DATE | 11. 28. 2005  | EDITION       | 3            |
| PAGE       | 4 OF 9        |               |              |

