

# 2/2 proportional directional valve, direct operated

**RE 18139-06/12.11** 1/12  
Replaces: 06.05

## Type KKDS (High Performance)

Component size 1  
Component series B  
Maximum operating pressure 350 bar  
Maximum flow 38 l/min

H6726

## Table of contents



| Contents  | Page |
|---|------|
| Features  | 1    |
| Ordering code   | 2    |
| Preferred types   | 2    |
| Function, cross-sections, symbols                               | 3    |
| Technical data  | 4, 5 |
| Characteristic curves   | 6    |
| Performance limits  | 7    |
| Minimum terminal voltage at the coil<br>and relative duty cycle | 8    |
| Unit dimensions   | 9    |
| Mounting cavity   | 10   |
| Available individual components                                 | 11   |

## Features

- Cartridge valve
  - Mounting cavity R/T-13A
  - Direct operated proportional valve for controlling the flow size
  - Operation by means of proportional solenoid with central thread and detachable coil
  - Rotatable solenoid coil
  - Free-flowing in both directions
  - With concealed manual override, optional
- | – Control electronics:                               | Data sheet |
|--|------------|
| • Plug-in proportional amplifier<br>type VT-SSPA1... | 30116      |
| • Analog amplifier type RA...                        | 95230      |

Information on available spare parts:  
[www.boschrexroth.com/spc](http://www.boschrexroth.com/spc)

## Ordering code

| KKDS   |   | R   | 1   | B / H              | C                    |                                     |   | V  | *  |
|--|---|---|-----|--------------------|----------------------|-------------------------------------|---|--|--|
| Proportional directional valve,<br>direct operated |   | Maximum operating pressure 350 bar = R                            |     | Component size = 1 |                      | 2 main ports                        |   | Further details in<br>the plain text   |  |
| Symbols  |  | normally closed   | = N |                    | Component series = B |                                     | High Performance and mounting cavity R/T-13A = H<br>(see page 10) |  | Seal material<br>FKM seals<br>Attention!<br>Observe compatibility of seals<br>with hydraulic fluid used! |
|  |  | normally open   | = P |                    |                      |                                     |   |  |  |
| Component series = B                               |   | High Performance and mounting cavity R/T-13A = H<br>(see page 10) |     | C =                |                      | V =                                 |   | Electrical connection <sup>1)</sup>  |  |
|  |   |   |     |                    |                      | N0 = Without manual override        |   | K4 = Without mating connector,<br>with connector<br>according to DIN EN 175301-803 |  |
|  |   |   |     |                    |                      | N9 = With concealed manual override |   | K40 = Without mating connector, with<br>connector DT 04-2PA (Deutsch plug)         |  |
|  |   |   |     |                    |                      |                                     |   | C4 = Without mating connector, with<br>connector AMP Junior-Timer                  |  |
|  |   |   |     |                    |                      |                                     |   | Supply voltage   |  |
|  |   |   |     |                    |                      | G24 = Control electronics 24 V DC   |   |  |  |
|  |   |   |     |                    |                      | G12 = Control electronics 12 V DC   |   |  |  |
|  |   |   |     |                    |                      | C = Proportional solenoid, wet-pin  |   |  |  |

<sup>1)</sup> Mating connectors, separate order, see data sheet 08006

## Preferred types

| Type                | Material no. |
|---------------------|--------------|
| KKDSR1NB/HCG24N0K4V | R901023172   |
| KKDSR1PB/HCG24N0K4V | R901024015   |
| KKDSR1NB/HCG12N0K4V | R901024009   |
| KKDSR1PB/HCG12N0K4V | R901024034   |

## Function, cross-sections, symbols

### General


The 2/2 proportional directional valve is a direct operated cartridge spool valve. It steplessly controls the flow from main port ① to ② and from ② to ① in proportion to the input signal. The valve basically consists of a bushing (6) with male thread for the mounting cavity, a socket (3), a control spool (5) with compression spring (8) as well as of a proportional solenoid (7) with central thread and removable coil.

### Function (version "N" – normally closed)



When the solenoid (7) is de-energized, the control spool (5) that is always pressure-compensated in relation to the actuating forces due to its constructive design, is held in the initial position by the compression spring (8) and blocks the flow between main port ① and ②. When the solenoid (7) is energized, the control spool (5) is adjusted directly – in proportion to the electrical input signal – and connects main port ① and ② via orifice-like cross-sections in the spool with progressive flow characteristics. When the solenoid (7) is de-energized, the compression spring (8) returns the control spool (5) to the initial position.

The manual override (4) allows for the switching of the valve without solenoid energization.

Symbol "N" – normally closed



Symbol "P" – normally open



**Technical data** (For applications outside these parameters, please consult us!)**general**

|                           |    |  |
|---------------------------|----|--|
| Weight                    | kg | 0.66   |
| Installation position     |    | Any - if it is ensured that no air can collect upstream of the valve. Otherwise, we recommend that the valve be mounted in a suspended position. |
| Ambient temperature range | °C | -40 to +100 (see minimum terminal voltage page 8)  |
| Storage temperature range | °C | -20 to +80   |

**Environmental audits**

|  |   |   |
|--|---|---|
| Salt spray test according to DIN 50021   | h | 720   |
| Surface protection proportional solenoid |   | Coating according to DIN 50962-Fe//ZnNi with thick film passivation |

**hydraulic**

|   |                              |   |
|---|------------------------------|---|
| Maximum operating pressure  | bar                          | 350   |
| Maximum flow  | – Symbol "N"<br>– Symbol "P" | l/min<br>l/min  |
|   |                              | 38 (① → ②), 34 (② → ①); other flows upon request!<br>32 (① → ②), 45 (② → ①) |
| Leakage   | ml/min                       | < 30 (at $\Delta p = 100$ bar in ①; HLP46, $\vartheta_{oil} = 40$ °C)       |
| Step response   | 0 to 100 %; 100 to 0 %       | ms  |
|   |                              | < 65 (at $p_s = 10$ bar)  |
| Hydraulic fluid   |                              | See table page 5  |
| Hydraulic fluid temperature range   | °C                           | -40 to +100 (preferably +40 to +50)   |
| Viscosity range   | mm <sup>2</sup> /s           | 5 to 400 (preferably 10 to 100)   |
| Maximum admissible degree of contamination of the hydraulic fluid cleanliness class according to ISO 4406 (c) |                              | Class 20/18/15 <sup>1)</sup>  |
| Hysteresis <sup>2)</sup>  | %                            | ≤ 5   |
| Range of inversion <sup>2)</sup>  | %                            | ≤ 2   |
| Response sensitivity <sup>2)</sup>  | %                            | ≤ 1   |
| Load cycles   |                              | 2 million   |

<sup>1)</sup> The cleanliness classes specified for the components must be complied with in hydraulic systems. An effective filtration prevents faults and at the same time increases the service life of the components.


For the selection of filters see [www.boschrexroth.com/filter](http://www.boschrexroth.com/filter).

<sup>2)</sup> Measured with analog amplifier type RA2-1/10, see data sheet 95230

## Technical data (For applications outside these parameters, please consult us!)

### hydraulic

| Hydraulic fluid                       | Classification             | Suitable sealing materials | Standards |
|---------------------------------------|----------------------------|----------------------------|-----------|
| Mineral oils and related hydrocarbons | HL, HLP, HLPD, HVLP, HVLDP | FKM                        | DIN 51524 |
| Environmentally compatible            | – Insoluble in water       | HEES                       | FKM       |
|                                       |                            | HEPR                       | FKM       |
|                                       | – Soluble in water         | HEPG                       | FKM       |
| Flame-resistant                       | – Water-free               | HFDU, HFDR                 | FKM       |
|                                       | – Water-containing         | HFAS                       | FKM       |

 **Important information on hydraulic fluids!**

- For more information and data on the use of other hydraulic fluids, refer to data sheet 90220 or contact us!
- There may be limitations regarding the technical valve data (temperature, pressure range, service life, maintenance intervals, etc.)!
- The flash point of the process and operating medium used must be 40 K higher than the maximum solenoid surface temperature.

- **Flame-resistant – water-containing:** Maximum pressure differential per control edge 175 bar, otherwise increased cavitation erosion!  
Tank pre-loading < 1 bar or > 20 % of the pressure differential. The pressure peaks should not exceed the maximum operating pressures!
- **Environmentally compatible:** When using environmentally compatible hydraulic fluids that are simultaneously zinc-soluble, zinc may accumulate in the medium (700 mg zinc per pole tube).





### electric

|  |                       |   |     |
|--|-----------------------|---|-----|
| Voltage type                               |                       | Direct voltage DC   |     |
| Supply voltage                             | V                     | 12  | 24  |
| Maximum solenoid current                   | A                     | 1.8   | 1.2 |
| Coil resistance                            | – Cold value at 20 °C | Ω   | 3.3 |
|  | – Max. hot value      | Ω   | 5.0 |
| Duty cycle                                 | %                     | 100 (see minimum terminal voltage page 8)   |     |
| Maximum coil temperature <sup>3)</sup>     | °C                    | 150   |     |
| Protection class according to DIN EN 60529 | – Version "K4"        | IP 65 with mating connector mounted and locked  |     |
|  | – Version "K40"       | IP 69K with mating connector mounted and locked   |     |
|  | – Version "C4"        | IP 66 with mating connector mounted and locked  |     |
|  |                       | IP 69K with Rexroth mating connector (material no. R901022127)  |     |
| Control electronics (separate order)       |                       | <ul style="list-style-type: none"> <li>– Plug-in proportional amplifier type VT-SSPA1..., see data sheet 30116</li> <li>– Analog amplifier type RA ..., see data sheet 95230</li> </ul> |     |
| Design according to VDE 0580               |                       |   |     |

<sup>3)</sup> Due to the surface temperatures of the solenoid coils, the standards ISO 13732-1 and EN 982 are to be observed!



**When establishing the electrical connection, the protective earthing conductor (PE  $\frac{1}{2}$ ) is to be connected properly.**

**Characteristic curves** (measured with HLP46,  $\vartheta_{oil} = 40 \text{ °C} \pm 5 \text{ °C}$ )



**Direction of flow ① → ②**  
**Symbol "N"**

**Direction of flow ② → ①**  
**Symbol "N"**

**Direction of flow ① → ②**  
**Symbol "P"**

**Direction of flow ② → ①**  
**Symbol "P"**


- 1  $\Delta p = 10$  bar constant
- 2  $\Delta p = 20$  bar constant
- 3  $\Delta p = 30$  bar constant
- 4  $\Delta p = 50$  bar constant
- 5  $\Delta p = 100$  bar constant

**Performance limits** (measured with HLP46,  $\vartheta_{oil} = 40 \text{ }^\circ\text{C} \pm 5 \text{ }^\circ\text{C}$ )





- 1 Command value = 40 %
- 2 Command value = 50 %
- 3 Command value = 60 %
- 4 Command value = 70 %
- 5 Command value = 80 %
- 6 Command value = 90 %
- 7 Command value = 100 %



- 1 Command value = 0 %
- 2 Command value = 10 %
- 3 Command value = 20 %
- 4 Command value = 30 %
- 5 Command value = 40 %
- 6 Command value = 50 %
- 7 Command value = 60 %
- 8 Command value = 70 %

## Minimum terminal voltage at the coil and relative duty cycle

### Admissible working range depending on the ambient temperature



■ Limited valve performance

**Notice!**


The characteristic curves have been determined for coils with valve and medium test block size (80 x 80 x 80 mm), without flow in calm air.

Depending on the installation conditions (block size, flow, air circulation, etc.), there may be a better heat dissipation. This results in an increased area of application.

In single cases, more unfavorable conditions may lead to limitations of the area of application.



## Unit dimensions (dimensions in mm)




① = Main port 1

② = Main port 2

LS = Location Shoulder

- 1 Mating connector without circuitry for connector "K4" (separate order, see data sheet 08006)
- 2 Space required for removing the mating connector
- 3 Concealed manual override "N9"
- 4 SW27, tightening torque  $M_A = 45$  to  $50$  Nm
- 5 Mating connector for connector "C4" (separate order, see data sheet 08006)
- 6 Mating connector for connector "K40" (separate order, see data sheet 08006)

**Mounting cavity R/T-13A<sup>1)</sup>; 2 main ports; thread M20 x 1.5 (dimensions in mm)**




- 1) Differing from T-13A
- 2) All seal ring insertion faces are rounded and free of burrs
- 3) With counterbore
- 4) Depth for moving parts

- ① = Main port 1
- ② = Main port 2
- LS = Location Shoulder

Tolerance for all angles  $\pm 0.5^\circ$

## Available individual components



| Item | Denomination                   |               | Direct voltage | Material no. |
|------|--------------------------------|---------------|----------------|--------------|
| 157  | Coil for individual connection | Version "K4"  | 12 V           | R901022180   |
|      |                                |               | 24 V           | R901022174   |
|      |                                | Version "K40" | 12 V           | R901272648   |
|      |                                |               | 24 V           | R901272647   |
|      |                                | Version "C4"  | 12 V           | R901022680   |
|      |                                |               | 24 V           | R901022683   |
| 158  | Nut                            |               | R900029574     |              |
| 159  | O-ring for pole tube           |               | R900071532     |              |
| 999  | Seal kit of the valve          |               | R900733593     |              |

## Notes

---

Bosch Rexroth AG  
Hydraulics  
Zum Eisengießer 1  
97816 Lohr am Main, Germany  
Phone +49 (0) 93 52 / 18-0  
Fax +49 (0) 93 52 / 18-23 58  
documentation@boschrexroth.de  
www.boschrexroth.de

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.