



Part no.: 50003188
TK 20x75
Reflector



Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50003188 – TK 20x75 – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	20.2 mm
Reflection surface width	15 mm
Mounting dimension, height	76 mm
Reflection surface height	70 mm
Mounting dimension, thickness	6.5 mm
Triple reflector size	2.6 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	8 g
Type of fastening	Adhesive

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

