

5S Solutions from DYMO

Meet your 5S needs with industrial labelling solutions from DYMO. Designed to work exclusively with Rhino label makers, DYMO IND labels are tough - jobsite tested and UL recognized. Whether you're labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO IND labels have you covered.



Rhino™ 6000
single S0773780 | kit S0771940



Rhino™ 5200
single S0841460 | kit S0841390



Rhino™ 4200
single S0955950



Rhino™ M1011
S0720090



IND Vinyl Labels

- Ideal for both indoor and outdoor applications
- Available in the widest range of OSHA, ANSI and ISO colour standards
- UL recognized as a component to UL 969
- RoHS compliant
- Length: 5.5 m



UV Resistant



Water Resistant



Temperature Resistant
-40° to 80° C



Oil Resistant



Chemical Resistant



IND VINYL LABELS FOR 5S			
Label Colour / Width	12 mm use with Rhino™ 4200, 5200, 6000	19 mm use with Rhino™ 4200, 5200, 6000	24 mm Rhino™ 6000
	DYMO #	DYMO #	DYMO #
A	18444	18445	1805430
A	18432	18433	1805431
A	18435	18436	1805427
A	1805413	1805419	1805425
A	1805416	1805422	1805429
A	1805435	1805436	1805432
A	1805414	1805420	1805426
A	1805243	1805417	1805423
A	1805415	1805421	1805428
A	1805412	1805418	1805424

IND Embossing Labels

- For heavy-duty, extreme condition labelling
- Ideal for marking pipelines, underground cables, engine parts, building materials and more
- Compatible with Rhino M1011 Embosser Kit only



IND METAL EMBOSSEING LABELS			
Label Material	12 mm Rhino™ M1011 only	Adhesive Strength	Length
	DYMO #		
Aluminium	31000	Non-Adhesive	4.80 m
Aluminium	35800	Adhesive	3.65 m
Stainless	32500	Non-Adhesive	6.40 m

The information contained in this 5S Guide is being provided for general information purposes only and the certifications referenced herein are based on current standards which are subject to change.