# MOSFET – Power, Single N-Channel 60 V, 21 mΩ, 27 A

#### Features

- Small Footprint (5x6 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- LFPAK4 Package, Industry Standard
- AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T <sub>J</sub> = 25°C unless otherwise noted)						
Parameter			Symbol	Value	Unit	
Drain-to-Source Voltage			V <sub>DSS</sub>	60	V	
Gate-to-Source Voltage	э		V <sub>GS</sub>	±20	V	
Continuous Drain Current R <sub>θJC</sub>	Steady State	$T_C = 25^{\circ}C$	۱ <sub>D</sub>	27	Α	
(Notes 1, 2, 3)	Sidle	T <sub>C</sub> = 100°C		15	1	
Power Dissipation		$T_{C} = 25^{\circ}C$	PD	28	W	
$R_{\theta JC}$ (Notes 1, 2)		$T_{C} = 100^{\circ}C$		9.0	]	
Continuous Drain	Steady State	$T_A = 25^{\circ}C$	۱ <sub>D</sub>	9.8	А	
Current R <sub>θJA</sub> (Notes 1, 2, 3)	Sidle	T <sub>A</sub> = 100°C		6.9		
Power Dissipation		$T_A = 25^{\circ}C$	PD	3.8	W	
R <sub>θJA</sub> (Notes 1 & 2)		$T_A = 100^{\circ}C$		1.9		
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \ \mu s$		I <sub>DM</sub>	131	А	
Operating Junction and Storage Temperature		T <sub>J</sub> , T <sub>stg</sub>	–55 to + 175	°C		
Source Current (Body Diode)		۱ <sub>S</sub>	23.5	А		
Single Pulse Drain-to-Source Avalanche Energy ( $I_{L(pk)} = 1.1 A$ )		E <sub>AS</sub>	43	mJ		
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		ΤL	260	°C		

#### MAXIMUM RATINGS (T<sub>.1</sub> = 25°C unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	5.3	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	39	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.


3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.




# **ON Semiconductor®**

## www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX	
60 V	21 mΩ @ 10 V	07.4	
	31.5 mΩ @ 4.5 V	27 A	





# ORDERING INFORMATION


See detailed ordering, marking and shipping information on page 5 of this data sheet.

## **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}C$ unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit	
OFF CHARACTERISTICS								
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, I <sub>D</sub> = 250 µA		60			V	
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>				28		mV/°C	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 V,$	T <sub>J</sub> = 25 °C			10		
		$V_{DS} = 60 V$	T <sub>J</sub> = 125°C			250	μΑ	
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA	
ON CHARACTERISTICS (Note 4)					-	-	-	
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_{D}$	= 16 μA	1.2		2.0	V	
Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				-5.0		mV/°C	
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 10 A		18	21	-	
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 10 A		26	31.5	mΩ	
Forward Transconductance	9 <sub>FS</sub>	V <sub>DS</sub> =15 V, I <sub>E</sub>	<sub>0</sub> = 10 A		37		S	
CHARGES AND CAPACITANCES								
Input Capacitance	C <sub>ISS</sub>				410			
Output Capacitance	C <sub>OSS</sub>	V <sub>GS</sub> = 0 V, f = 1 M⊢	lz, V <sub>DS</sub> = 25 V		210		pF	
Reverse Transfer Capacitance	C <sub>RSS</sub>				7.0		1	
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 48 V; I <sub>D</sub> = 10 A			2.5		nC	
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS}$ = 10 V, $V_{DS}$ = 48 V; $I_{D}$ = 10 A			5.0		nC	
Threshold Gate Charge	Q <sub>G(TH)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 48 V; I <sub>D</sub> = 10 A			0.6			
Gate-to-Source Charge	Q <sub>GS</sub>				1.0		nC V	
Gate-to-Drain Charge	Q <sub>GD</sub>				0.5			
Plateau Voltage	V <sub>GP</sub>				2.7			
SWITCHING CHARACTERISTICS (Note 5	5)				•			
Turn-On Delay Time	t <sub>d(ON)</sub>				4.0			
Rise Time	t <sub>r</sub>	Vce = 10 V. Vc	e = 48 V.		12		1	
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$I_D = 10 \text{ A}, \text{ R}_G$	$V_{GS}$ = 10 V, $V_{DS}$ = 48 V, I <sub>D</sub> = 10 A, R <sub>G</sub> = 2.5 $\Omega$		12		ns	
Fall Time	t <sub>f</sub>				1.5			
DRAIN-SOURCE DIODE CHARACTERIS	TICS					1	1	
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	$T_J = 25^{\circ}C$		0.9	1.2		
		$I_{\rm S} = 10  \text{A}$ $T_{\rm J} = 125^{\circ}$			0.8		V	
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dI <sub>S</sub> /dt = 100 A/µs, I <sub>S</sub> = 10 A			18			
Charge Time	ta				9.0		ns	
Discharge Time	t <sub>b</sub>				9.0		1	
Reverse Recovery Charge	Q <sub>RR</sub>				7.0		nC	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Pulse Test: pulse width  $\leq 300 \ \mu$ s, duty cycle  $\leq 2\%$ . 5. Switching characteristics are independent of operating junction temperatures.

## **TYPICAL CHARACTERISTICS**



## **TYPICAL CHARACTERISTICS**



# **TYPICAL CHARACTERISTICS**




Figure 13. Thermal Characteristics

## **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NVMYS021N06CLTWG	021N06CL	LFPAK4 (Pb–Free)	3000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


#### PACKAGE DIMENSIONS

A4

NOTES:


- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  CONTROLLING DIMENSION:
- 2. CONTROLLING DIMENSION: MILLIMETERS.
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
  DATUMS A AND B ARE
  - DETERMINED AT DATUM PLANE H.

U	UNIT IN MILLIMETER				
DIM			MAX		
Α	1.10	1.20	1.30		
A1	0.00	0.08	0.15		
A2	1.10	1.15	1.20		
A3		0.25			
A4	0.45	0.50	0.55		
b	0.40	0.45	0.50		
b2	3.80	4.10	4.40		
b3	2.00	2.10	2.20		
b4	0.70	0.80	0.90		
С	0.19	0.22	0.25		
c2	0.19	0.22	0.25		
D	4.05	4.15	4.25		
D1	-	-	4.20		
D2	3.0	3.10	3.20		
D3	0.30	0.40	0.50		
E	4.80	4.90	5.00		
E1	3.10	3.20	3.30		
E2	5.00	5.15	5.30		
е	1.27 BSC				
Н	6.00	6.15	6.30		
L	0.40	0.65	0.85		
L1	0.80	0.90	1.00		
L2	0.80	1.05	1.30		
q	0°	4°	8°		



0.10 C

A1



A3

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor roducts, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

Order Literature: http://www.onsemi.com/orderlit

ON Semiconductor Website: www.onsemi.com

For additional information, please contact your local Sales Representative