

Product Datasheet

Product code: **E5342.CR.BG**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5342 is a high precision cutter belonging to the small tapered cutter family. This type of geometry and head dimensions offer an advantage to access small areas. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5342 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Small Tapered

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.10-1.00 mm (38-18 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek - Thermoplastic Elastomer + PP compound

Picture:



Dimensions: OAL (A) 125.0 mm – 4.921 inch
 Width 60.0 mm – 2.362 inch
 Height 21.0 mm – 0.827 inch

Head dimensions: Width (C) 10.0 mm – 0.394 inch
 Thickness (D) 6.4 mm – 0.252 inch
 B 9.0 mm – 0.354 inch
 F 0.2 mm – 0.008 inch

