

# 12 Watt

- Energy Efficiency Level VI
- European CoC Tier 2
- Interchangeable Mains Connectors Included
- Universal Input
- Output Voltages from 5.0 V to 12.0 V
- Class II Construction
- Low Cost





The VER12 series of wall plug adaptors comply with the very latest energy efficiency VI standards with high active mode efficiency and extremely low no load power consumption. Available with a standard jack plug connector these adaptors suit a wide variety of cost sensitive applications while maintaining industry leading performance.

### Dimensions:

**VER (body only):** 3.01 x 1.61 x 1.48" (76.5 x 41.0 x 37.6 mm)

## **Models & Ratings**

Output Power	Output Voltage	Output Current	Total Regulation(2)	Output Connector	Model Number
	5.0 V	2100 mA	5%	5.5 x 2.1 x 12 mm DC Jack	VER12US050-JA
12 W	9.0 V	1280 mA	5%	5.5 x 2.1 x 12 mm DC Jack	VER12US090-JA
	12.0 V	1000 mA	5%	5.5 x 2.1 x 12 mm DC Jack	VER12US120-JA

#### Notes

2. Total regulation includes initial set accuracy, line and load regulation.

Input					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage	90		264	VAC	
Input Frequency	47		63	Hz	
Input Current			0.3	A	100 VAC
Inrush Current			60	А	240 VAC, cold start at 25 °C
Power Factor					EN61000-3-2, class A
No Load Input Power			0.1	W	
Input Protection	Internal T1.0A/25	0 VAC fuse			

Output					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	5.0		12.0	V	See Models and Ratings table
Minimum Load	0			А	No minimum load required
Start Up Delay			4	S	
Start Up Rise Time		30		ms	
Hold Up Time	10			ms	Full load and 100 VAC
Total Regulation			5	%	See Models and Ratings table
Transient Response			4	% deviation	Recovery within <1% within 500 μs for a 60% step load change at 0.15 A/μs
Ripple & Noise			150	mV pk-pk	Measured with 20 MHz bandwidth and 47 μF electrolytic in parallel with 0.1 μF ceramic capacitor
Short Circuit Protection					Continuous, trip and restart (hiccup mode) with auto recovery
Temperature Coefficient			0.05	%/°C	

<sup>1.</sup> Other output voltages available, contact sales for details.

# **VER12 Series**





# General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		79/83		%	5 V/9 V, 12 V typical average of efficiencies measured at 25%, 50%, 75% and 100% load and 115 VAC input
Energy Efficiency					Level VI
Isolation		3000		VAC	Input to Output
Switching Frequency	24		70	kHz	Variable
Mean Time Between Failure	100			kHrs	MIL-HDBK-217F at 25 °C GB
Weight		0.28 (80)		lb (g)	Body only

# Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	0		+60	°C	Derate from 100% load at 40 °C to 50% load at 60 °C
Storage Temperature	-40		+85	°C	
Operating Humidity	5		95	%	RH, non-condensing
Cooling					Natural convection
Shock					1 m drop onto concrete on each of 6 axes
Vibration	10		300	Hz	2 g 15 mins/sweep, 60 mins for each of 3 axes

# **EMC: Emissions**

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55032	Level B	
Radiated	EN55032	Level B	
Harmonic Current	EN61000-3-2	Class A	
Voltage Flicker	EN61000-3-3		

# **EMC: Immunity**

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions	
ESD Immunity	EN61000-4-2	2,3	А	±4 kV contact, ±8 kV air	
Radiated Immunity	EN61000-4-3	3 V/m	А		
EFT/Burst	EN61000-4-4	Level 2	A		
Surge	EN61000-4-5	Level 2	А		
Conducted Immunity	EN61000-4-6	3 V	A		
Magnetic Fields	EN61000-4-8	1 A/m	А		
Dips and Interruptions	EN55035 100% 10 ms, 30% 500 ms, 100% 5000 ms, Perf Criteria A, A, B				


# **Safety Approvals**

Safety Certification	Standard			
CB Report	IEC60950-1, IEC62368-1			
UL	UL62368-1			
EN	EN60950-1, EN62368-1			
CCC	China Compulsory Certification, GB4943			
AU/NZ	AU/NZ 60950.1			
CE	Meets all applicable directives			
UKCA	Meets all applicable legislation			




## **Mechanical Details**

#### **VER12US**




## **AC Input Plugs**


## **UK Plug**




### **US Plug**



## **AU Plug**



## **EU Plug**







**Mechanical Details** 

## **AC Input Plugs**

## **CCC Plug**



## **Output Lead and Connection**



Wire type: VW-1 80°C 300 V L=1500 mm 2468 20 AWG for 5 V output, 22 AWG for 9 V output, 24 AWG for 12 V output, 2C Black and White. Black - Negative, White - Positive

