

SCSC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application


For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17830 840
ISO name	SCSC R/L 1616 H12
Shaft height	16 mm
Shank width	16 mm
Length	100 mm
Length of head	22 mm
Programming size	20 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Right

EAN-Code

4050293562880