



# Wide-mouth jerrycan 11 L, HD-PE

## natural-coloured, with UV protection



### Description:

Wide-mouth jerrycans 11 litres, natural-colour, made of unbreakable polyethylene (HD-PE) professional design for versatile implementation

- very large opening (88 mm diameter) allows easy filling, emptying and cleaning
- undetachable, sealable wide-mouth screw cap
- useful as settling bottle
- with gripping surface on the base for secure handling
- with additional, small spout (diameter 18 mm) and spout nozzle
- resistant to greases, resins, alkalis, oils and acids
- UV protection for long life
- opening sealed with screw plug for screwing in spigots and corner valves (wide thread 22 mm)
- on request: Custom-made product without screw plug opening, print, labelling, individual scales and colours possible
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- w = inside diameter of filling opening = 88 (18) mm / a = outside thread diameter = 105 (24) mm
- t = depth = 132 mm b = width = 264 mm (277 mm with lid) h = height = 426 mm (435 mm with lid)
- Successor article of Art.-No. 818100 with new dimensions

### Information:

#### Article

Articlenumber	<b>818110</b>
GTIN	<b>4007228818116</b>
Customs tariff	<b>39233090</b>
Packaging Unit (PU)	<b>5</b>

Colour	<b>natural</b>
Volume in l	<b>11</b>
Weight (kg)	<b>0,91</b>
T x B x H (mm)	<b>132 x 277 x 435</b>

#### Outer packaging

Content in pieces	<b>5</b>
L x B x H (mm)	<b>518 x 335 x 680</b>

Gross weight unit (kg)	<b>5,16</b>
EAN Verpackungseinheit	<b>4007228412147</b>

#### Pallet

Number of boxes	<b>15</b>
Number of layers	<b>3</b>
L x B x H (m)	<b>1,2 x 0,8 x 2,19</b>

Carton per layer	<b>5</b>
Gross Weight Palette (kg)	<b>97,4</b>