



NH-FUSE-BASE WITH MICROSWITCH 400A 1000V
SIZE 2L FOR PHOTOVOLTAIC APPLICATION

Model		
product brand name		SENTRON
Design of the product		3NH LV HRC fuse bases
General technical data		
Number of poles		1
Size of fuse system / acc. to DIN EN 60269-1		NH2L
Electricity		
rated current I_n / IEC, DIN/VDE / at 40 Cel	A	368
Current / with AC / Rated value	A	400
Product details		
Product component / Swivel mechanism		Yes
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	20
Type of electrical connection • for main current circuit		for mounting on mounting plate flat connector
Mechanical Design		
Height	mm	326
Depth	mm	170
Mounting type		fixed mounting
Mounting type / bus-mounting		No



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NH73604KK01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NH73604KK01/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NH73604KK01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015