Fork Sensor

YH08NCT8 LASER


Part Number



- Fine light beam (0,6 mm) over entire width of fork
- **Recognition of transparent objects** •
- Repetition accuracy: 5 µm •
- Teach-in

The transmitter and the receiver are integrated into a single housing as a light barrier. If the active light beam between the transmitter and the receiver is interrupted, the output is switched accordingly.

Thanks to the use of visible laser light, the sensor is very easy to align to the object. The use of a fine light beam ensures a small diameter spot over the entire width of the fork. This allows for the recognition of extremly small parts, holes, slots and notches.




Technical Data


Optical Data					
Fork Width	80 mm				
Smallest Recognizable Part	40 <i>µ</i> m				
Smallest Detectable Gap	50 μm				
Switching Hysteresis	< 20 µm				
Light Source	Laser (red)				
Wavelength	655 nm				
Service Life (T = +25 °C)	100000 h				
Laser Class (EN 60825-1)	2				
Max. Ambient Light	10000 Lux				
Light Spot Diameter	0.6 mm				
Repeat Accuracy	< 5 µm				
Electrical Data	,				
Supply Voltage	1030 V DC				
Current Consumption (Ub = 24 V)	< 50 mA				
Switching Frequency	10 kHz				
Response Time	50 µs				
Off-Delay	0100 ms				
Temperature Range	-2560 °C				
Switching Output Voltage Drop	< 1,5 V				
NPN Switching Output/Switching Current	200 mA				
internal Load Switching Output	5100 Ohm				
Short Circuit Protection	yes				
Reverse Polarity Protection	yes				
Overload Protection	yes				
Teach Mode	NT, MT				
Protection Class	III				
FDA Accession Number	0820592-000				
Mechanical Data					
Setting Method	Teach-In				
Housing Material	Plastic; Steel, nickel- plated				
Full Encapsulation	yes				
Degree of Protection	IP67				
Connection	M8 × 1; 3-pin				
Safety-relevant Data					
MTTFd (EN ISO 13849-1)	1436,4 a				
NPN NO/NC switchable					
Connection Diagram No.	358				
Control Panel No.	H1				
Suitable Connection Equipment No.	8				

Photoelectronic Sensors










01 = Switching Status Indicator 02 = Contamination Warning 06 = Teach Button

07 = Selector Switch

Screw M4 = 1 Nm All dimensions in mm (1 mm = 0.03937 Inch)



Legen	d		PŤ	Platinum measuring resistor	ENA	ARS422 Encoder A/Ā (TTL)
+	Supply Voltage +		nc	not connected	ENE	BR5422 Encoder B/B (TTL)
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENE	B Encoder B
А	Switching Output (NO)		W	Trigger Input	Ами	 Digital output MIN
Ā	Switching Output (NC)		W -	Ground for the Trigger Input	Ама	x Digital output MAX
V	Contamination/Error Output (NO)		0	Analog Output	Аок	Digital output OK
V	Contamination/Error Output (NC)		0-	Ground for the Analog Output	SY	In Synchronization In
E	Input (analog or digital)		ΒZ	Block Discharge	SYO	JUT Synchronization OUT
Т	Teach Input		Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)		а	Valve Control Output +	м	Maintenance
S	Shielding		b	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path		SY	Synchronization	Wire	e Colors according to DIN IEC 757
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black
RDY	Ready		E+	Receiver-Line	BN	Brown
GND	Ground		S+	Emitter-Line	RD	Red
CL	Clock		÷	Grounding	OG	Orange
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow
۲	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey
Signal	Signal Output		Mag	Magnet activation	WH	H White
BI_D+/-	Ethernet Gigabit bidirect, data line (A	D)	RES	Input confirmation	PK	
ENO RS422	Encoder 0-pulse 0-0 (TTL)		EDM	Contactor Monitoring	GN	YE Green/Yellow

