

Double Row Terminal Blocks

200 Series Kulka® 671 GP Series 300 Volts AC/DC (Class B)



206 / 671 GP 06

Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Closed Back Design
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-30 Poles
- 7/16" Centers
- Wire Range With Wire Binding Screw
#12 - #22 AWG – 20 Amps
- Wire Range With Sems Pressure Screw #12 - #22 AWG
Stranded Copper Wire Only, 20 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

| MSP Catalog # | Kulka® Catalog # | # of poles | Dimensions | |
|------------------|---------------------|------------|------------|-------|
| | | | A | B |
| 201 | 671 GP 01 | 1 | 1.19 | 0.88 |
| 202 | 671 GP 02 | 2 | 1.62 | 1.31 |
| 203 | 671 GP 03 | 3 | 2.06 | 1.75 |
| 204 | 671 GP 04 | 4 | 2.50 | 2.19 |
| 205 | 671 GP 05 | 5 | 2.94 | 2.63 |
| 206 | 671 GP 06 | 6 | 3.37 | 3.06 |
| 207 | 671 GP 07 | 7 | 3.81 | 3.50 |
| 208 | 671 GP 08 | 8 | 4.25 | 3.94 |
| 209 | 671 GP 09 | 9 | 4.69 | 4.38 |
| 210 | 671 GP 10 | 10 | 5.12 | 4.81 |
| 211 | 671 GP 11 | 11 | 5.56 | 5.25 |
| 212 | 671 GP 12 | 12 | 6.00 | 5.69 |
| 213 | 671 GP 13 | 13 | 6.44 | 6.13 |
| 214 | 671 GP 14 | 14 | 6.87 | 6.56 |
| 215 | 671 GP 15 | 15 | 7.31 | 7.00 |
| 216 | 671 GP 16 | 16 | 7.75 | 7.44 |
| 217 | 671 GP 17 | 17 | 8.19 | 7.88 |
| 218 | 671 GP 18 | 18 | 8.62 | 8.31 |
| 219 | 671 GP 19 | 19 | 9.06 | 8.75 |
| 220 | 671 GP 20 | 20 | 9.50 | 9.19 |
| 221 | 671 GP 21 | 21 | 9.94 | 9.63 |
| 222 | 671 GP 22 | 22 | 10.37 | 10.06 |
| 223 | 671 GP 23 | 23 | 10.81 | 10.50 |
| 224 | 671 GP 24 | 24 | 11.25 | 10.94 |
| 225 | 671 GP 25 | 25 | 11.69 | 11.38 |
| 226 | 671 GP 26 | 26 | 12.12 | 11.81 |
| 227 | 671 GP 27 | 27 | 12.56 | 12.25 |
| 228 | 671 GP 28 | 28 | 13.00 | 12.69 |
| 229 | 671 GP 29 | 29 | 13.44 | 13.13 |
| 230 | 671 GP 30 | 30 | 13.87 | 13.56 |

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

| CATALOG # | PRODUCT DESCRIPTION | PAGE REFERENCE |
|-----------|--|--------------------------|
| F1 | Full Quick Connect (0° Flat) | See page 105 |
| F2 | Full Quick Connect (45° Bend) | See page 105 |
| F3 | Full Quick Connect (90° Bend) | See page 105 |
| HF1 | Half Quick Connect (0° Flat) | See page 105 |
| HF2 | Half Quick Connect (45° Bend) | See page 105 |
| HF3 | Half Quick Connect (90° Bend) | See page 105 |
| S | Full Solder | See page 106 |
| HS | Half Solder | See page 106 |
| L | Feed Thru Solder (.437) | See page 106 |
| LSL | Feed Thru Solder (.625) | See page 106 |
| LL 200 | Line to Line Jumper | See page 107 |
| | 601RJ(S) | Multiple Position Jumper |
| SP | SEMS Pressure Saddle Screw | See page 107 |
| SPSE | SEMS Pressure Saddle Screw with External Tooth Lock Washer | Consult C/S |
| LWW | Feed Thru Wire Wrap (.640) | Consult C/S |
| PSB | Phil-Slot Brass Screw | Consult C/S |

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

