

## Fixed centring point

Carbide-tipped point

**ORION**<sup>®</sup>

### Application:


For centring and supporting long and narrow workpieces on lathes and grinding machines.

### Execution:

- Tip angle 60°.
- Carbide-tipped.
- Precision-ground.

### Advantage:

- Wear-resistant carbide tip.



<b>Art. no.</b>	<b>22107 050</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22107050
<b>Morse taper size</b>	MK 5
<b>Programming size</b>	70.5 mm
<b>Diameter of flat area</b>	18 mm
<b>Outer diameter</b>	44.7 mm
<b>DIN</b>	806
<b>Gross Weight</b>	1.900 kg
<b>Product Group</b>	211

### EAN

4039247140077