

## Collet type ER

### Application:

For drilling and centring tools.

### Execution:

- For NC lathes
- Burnished
- For suitable collets, see no. 23320
- No. 23308 008-020 ring profile key for tightening and loosening.

<b>Art. no.</b>	<b>22782 020</b>
<b>Brand</b>	EWS
<b>Manufacturer Part Number</b>	135932
<b>VDI mount diameter</b>	20 mm
<b>Collet type</b>	ER 16
<b>Min./max. clamping range</b>	0.5-10 mm
<b>Projecting length</b>	40 mm
<b>Outer diameter</b>	50 mm
<b>Gross Weight</b>	0.294 kg
<b>Product Group</b>	215

