

Description

Very fast curing, high strength anaerobic adhesive for locking threads and retaining of cylindrical components. Suitable for curing on passive metal surfaces, zincchromated steel and stainless steel without activator.

Highly resistant to heat, corrosion, vibrations, water, gases, oils, hydrocarbons, and many chemicals.

Physical properties

Composition :	anaerobic methacrylate
Colour :	green
Fluorescence :	under blue light
Viscosity (+25°C - mPa s) :	3.000 - 5.000
Specific weight (+25°C - g/ml) :	1,1
max diameter of thread/ gap filling :	M36/1 ½ "/0,20 mm
Flash point :	> +100°C
Shelf life +25°C :	1 year in original unopened packaging

Curing performance

Curing rate depends on the assembly clearance, material surfaces and temperature. Functional strength is usually reached in 1 - 3 hours and full curing takes 24 - 36 hours. In case of passive surfaces and/or low temperature a fast cure can be obtained using Loxeal activator 11.

Curing properties

Bolt M10 x 20 Zn - quality 8.8 - nut h = 0,8 d at +25°C :	
Handling cure time :	2 - 5 minutes
Functional cure time :	1 - 2 hours
Full cure time :	3 - 6 hours
Locking torque	
breakaway :	30 - 35 N m
prevailing :	55 - 70 N m
Shear strength(ISO 10123) :	15 - 25 N/mm ²
Temperature range :	-55°C/+200°C

Directions for use

The product is recommended for use on metal surfaces. Clean and degrease parts before bonding with Loxeal Cleaner 10.

Apply product to fill completely the gap, assemble parts and hold on for curing time. Liquid product can damage coating, some plastics and elastomers and late stress-cracking events might be induced if used with some thermoplastics.

For application on non metal materials, contact Loxeal Technical Service. For disassembly, use normal tools and eventually heat pieces at +150°C/+250°C, remove any residue of cured product mechanically and clean parts with Acetone.

Storage

Keep product in a cool and dry room at no more than +25°C. To avoid contaminations do not refill containers with used product. For further information on applications, storage and handling contact Loxeal Technical Service

Safety and handling

Consult Material Safety Data Sheet before use.

Note

The data contained herein, obtained in Loxeal laboratories, are given for information only; if specifics are required, please contact Loxeal Technical Department. Loxeal ensures abiding quality of supplied products according to its own specifics. Loxeal cannot assume responsibility for the results obtained by others which methods are not under Loxeal control. It is user's responsibility to determine suitability for user's purpose of any product mentioned herein. Loxeal disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Loxeal products. Loxeal specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.