

SVJC clamp holder for lathes, positive

For longitudinal and copy turning using VC indexable inserts

ATORN[®]

Application

For longitudinal and copy turning using VC 35° indexable inserts



Version

- Precision-made steel support, bronzed, hardened, type V, pitch angle 93°, tip angle 35°, clearance angle 7°

Art. no.	17829 102
ISO name	SVJC R/L 1010 X11-A
Shaft height	10 mm
Shank width	10 mm
Length	115 mm
Programming size	10 mm
Suitable for indexable inserts	VC.. 1103..
Tool design	Right
DIN	4983

EAN-Code

4050293693065