

SITOR FUSE-LINK SIZE 1 100A, AC 1000V



Figure similar

| Model | | |
|--|----|--------------------------|
| product brand name | | SETRON |
| Design of an identification indicator | | front indicator |
| Design of the fuse link | | SITOR, LV HRC design |
| General technical data | | |
| Size of fuse system / acc. to DIN EN 60269-1 | | NH1 |
| Operating class of the fuse link | | aR |
| circuit-breaker / Design | | 3NE |
| Switching capacity | | |
| Switching capacity current | | |
| <ul style="list-style-type: none"> acc. to IEC 60947-2 / Rated value | kA | 100 |
| Dissipation | | |
| Active power loss | | |
| <ul style="list-style-type: none"> for rated value of the current / with AC / in hot operating state / per pole | W | 28 |
| Electricity | | |
| rated current I_n / IEC, DIN/VDE / at 40 Cel | A | 100 |
| Current / with AC / Rated value | A | 100 |
| Mechanical Design | | |
| mounting position | | Any, preferably vertical |
| Environmental conditions | | |
| Ambient temperature | | |
| <ul style="list-style-type: none"> minimum | °C | -20 |

• maximum

°C 50

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity



CCC

GOST

UL

EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NE3221>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NE3221/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE3221

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015